

## HEPA Filtered Vacuums



AV-4POLY



AV-2



AV-5



AV-15



Hazardous material vacuums are equipped with a HEPA filter system consisting of a certified HEPA filter, a double layer intermediate micro filter, and a totally enclosed 2-ply disposable paper bag filter. The HEPA filter is made of high strength microfibred glass paper separated by corrugated aluminum sheeting that is entrapped in a steel screen. All HEPA filters are rated with a minimum efficiency of 99.97% at 0.3 microns and tested using the HOT DOP method @ 100 cfm, UL 586 certified, maximum 1" resistance. Models AV-2 and AV-15 motor heads are provided with a remote exhaust port for 1½" or 2" hose. All motors have a 2 year warranty. All Certified HEPA filters meet or exceed the following standards: IEST-RP-CC007; UL-586; MILF-561079; ANSI-2-92.

### All Electric HEPA Vacuums Include:

120 VAC, 60 Hz, 2 stage by-pass motor, HEPA filter, 94 - 115 cfm, 84" - 110" water lift, 30 foot power cord with plug. **Also includes:** 10 foot hose (1½"), HEPA filter, intermediate pre-filter, 2-ply disposable paper filter bag, and tool kit (5 foot curved steel wand, 10 foot vacuum hose with end cuffs, crevice tool, inlet swivel connector, and hard floor brush).

### 2 to 15 Gallon Electric HEPA Filtered Vacuums

Item No.	Description
AV-2	2 gallon recovery tank, 1.3 HP
AV-2BP	2 gallon recovery tank, 1.3 HP with back pack frame
AV-4POLY	4 gallon recovery tank, 1.3 HP, wheel kit
AV-5	5 gallon recovery tank, 1.3 HP, wheel kit
AV-15	15 gallon recovery tank, 2.3 HP, wheel kit, and tool kit

### Vacuum Accessories

Item No.	Description
AV-4POLYTN	Pneumatic beater bar, 1.25", for AV-4POLY
AV-335150	Electric beater bar, 17" for AV-5, AV-15 & AV-55 models
AV-15WP	Wet conversion kit for AV-15 & AV-55 models

### 55 Gallon HEPA Vacuums

Item No.	Description
AV-55	Electric motor 55 gallon drum lid assembly with HEPA filter, 1½" hose connection, hose, and 2.3 HP - <b>Order drum and dolly separately</b>
AV-55P	Pneumatic motor 55 gallon drum lid assembly with HEPA filter, 1½" hose connection, hose - <b>Order drum and dolly separately</b>
AV-55P-CND	Pneumatic motor 55 gallon drum lid assembly with HEPA filter, 1½" conductive 10 foot hose, steel 55 gallon drum, drum dolly, filters, accessory tools and ground wires, all ground wires connected

55 Gallon HEPA Vacuum AV-55P-CND



### 55 Gallon Vacuum - Drum and Accessories

Item No.	Description
AV-55DH	55 gallon drum - Black
AV-55DD	Drum dolly with wheels and handle for 55 gallon drum
AV-105	Goose neck hose adapter for 55 gallon drum lid, fits 1½" hose



55 Gallon Dolly Drum AV-55DD