

## 12" Axial Fans and Kits For Non-Hazardous Locations



12" Axial Fan  
CVF-12AC



12" Axial Canister Fan  
CVF12CAN15

**Certified for Outdoor Use**

Model	Model No.	Free Air	15' 1-90° Bend	15' 2-90° Bends
12" AC Fan (60 Hz)	CVF-12AC	2,348 CFM	1,868 CFM	1,690 CFM
12" AC Fan (50 Hz)	CVF-12AC50	1,956 CFM	1,557 CFM	1,408 CFM

### Applications

- Confined Spaces
- Construction / Maintenance
- Utility Companies
- Shipbuilding / Repair
- Manhole Entry
- Underground Vaults
- Construction / Maintenance
- Electrical Transformer Repair
- Open Trenching

12" Axial Fans are made from rugged, lightweight polyethylene, providing fresh air for confined space ventilation.

### 12" Axial Fans

Item No.	Description
CVF-12AC	12" AC Axial Fan - 1 HP, 115 VAC, 50/60 Hz, GFCI plug. CSA C/US Certified. CE Registered. 28 lbs.
CVF-12AC50	12" AC Axial Fan - 1 HP, 230 VAC, 50 Hz, user specifies plug. CE Registered. 28 lbs.

### 12" Axial Canister Fans

Item No.	Description
CVF12CAN15	12" CVF-12AC Axial Fan, 15 foot duct canister
CVF12CAN25	12" CVF-12AC Axial Fan, 25 foot duct canister
<b>Duct Canister Only - Fits 12" CVF Fans</b>	
CVFCAN1215	12" Duct canister, 15 foot duct
CVFCAN1225	12" Duct canister, 25 foot duct

### The Saddle Vent® Non-Hazardous Locations

Item No.	Description
SV-18912-O	12" Industrial Saddle Vent® - orange
SV-UM	Universal Saddle Vent® mounting bracket - steel

12" Saddle Vent®  
SV-18912-O



Saddle Vent® Mount  
SV-UM

