

ALLOY CHAIN FITTINGS

GRADE 100

CLEVIS SHORTENING CLUTCH

| For Chain Size | Part # | Dimensions (in) | | | | | | | | | | | Weight (lbs) | WLL (lbs) |
|----------------|---------|-----------------|------|------|------|------|------|------|-------|------|------|-----------|--------------|-----------|
| | | A | B | C | D | E | F | G | H | I | M | PxL | | |
| 9/32 | CXXL07S | 0.37 | 0.37 | 0.39 | 0.37 | 0.93 | 2.20 | 1.14 | 6.22 | 0.33 | 1.75 | 0.35x1.34 | 1.81 | 4,300 |
| 5/16 | CXXL08S | 0.37 | 0.37 | 0.39 | 0.37 | 0.93 | 2.20 | 1.14 | 6.46 | 0.39 | 1.97 | 0.39x1.34 | 1.87 | 5,700 |
| 3/8 | CXXL10S | 0.47 | 0.47 | 0.57 | 0.47 | 1.28 | 3.07 | 1.42 | 7.60 | 0.49 | 2.38 | 0.51x1.54 | 3.55 | 8,800 |
| 1/2 | CXXL13S | 0.61 | 0.61 | 0.71 | 0.61 | 1.73 | 3.54 | 1.38 | 9.82 | 0.63 | 2.99 | 0.63x2.09 | 7.21 | 15,000 |
| 5/8 | CXXL16S | 0.75 | 0.83 | 0.83 | 0.75 | 1.97 | 4.17 | 1.50 | 11.93 | 0.79 | 3.82 | 0.83x2.76 | 12.68 | 22,600 |

Hook Markings:

Size and Grade
7 for 7mm
10 for G100 (or 8 for G80)

Inch size in fractions

Production Code

Hallmark H-92 & CE
(European quality markings)

Manufacturers brand name

Part Number

ALLOY CHAIN FITTINGS

GRADE 80

CONNECTING LINK

| For Chain Size | Part # | Dimensions (in) | | | | | | | Weight (lbs) | WLL (lbs) |
|----------------|--------|-----------------|------|------|------|------|------|-------|--------------|-----------|
| | | A | C | O | R | P | S | | | |
| 7/32 | CL06 | 0.63 | 0.71 | 0.65 | 1.69 | 0.28 | 0.27 | 0.15 | 2,500 | |
| 9/32 | CL07 | 0.73 | 0.79 | 0.79 | 1.93 | 0.33 | 0.30 | 0.22 | 3,500 | |
| 5/16 | CL08 | 0.89 | 1.02 | 0.98 | 2.76 | 0.37 | 0.35 | 0.55 | 4,500 | |
| 3/8 | CL10 | 0.98 | 1.26 | 1.06 | 3.03 | 0.47 | 0.43 | 0.77 | 7,100 | |
| 1/2 | CL13 | 1.18 | 1.38 | 1.26 | 3.35 | 0.61 | 0.61 | 1.50 | 12,000 | |
| 5/8 | CL16 | 1.30 | 1.57 | 1.54 | 4.06 | 0.83 | 0.83 | 2.43 | 18,100 | |
| 3/4 | CL20 | 1.73 | 1.89 | 1.85 | 4.57 | 0.91 | 0.91 | 3.75 | 28,300 | |
| 7/8 | CL22 | 1.93 | 2.01 | 2.17 | 5.24 | 1.04 | 1.04 | 4.85 | 34,200 | |
| 1 | CL26 | 2.36 | 2.36 | 2.60 | 5.83 | 1.24 | 1.24 | 9.26 | 47,700 | |
| 1-1/4 | CL32 | 3.15 | 3.03 | 3.39 | 7.48 | 1.57 | 1.26 | 15.85 | 72,300 | |

CLEVIS SLING HOOK WITH FORGED LATCH

| For Chain Size | Part # | Dimensions (in) | | | | | | | | | Weight (lbs) | WLL (lbs) |
|----------------|--------|-----------------|------|------|------|------|------|------|------|-------|--------------|-----------|
| | | A | A1 | B | C | G | H | P | R | | | |
| 7/32 | CB06SF | 0.98 | 0.75 | 0.26 | 0.33 | 0.57 | 0.79 | 0.28 | 2.87 | 0.53 | 2,500 | |
| 9/32-5/16 | CB08SF | 1.16 | 0.96 | 0.34 | 0.39 | 0.75 | 1.06 | 0.35 | 3.40 | 1.17 | 4,500 | |
| 3/8 | CB10SF | 1.41 | 1.14 | 0.48 | 0.53 | 0.93 | 1.30 | 0.51 | 4.13 | 2.09 | 7,100 | |
| 1/2 | CB13SF | 1.71 | 1.38 | 0.60 | 0.67 | 1.12 | 1.57 | 0.63 | 5.06 | 3.68 | 12,000 | |
| 5/8 | CB16SF | 2.20 | 1.77 | 0.71 | 0.87 | 1.46 | 1.89 | 0.79 | 6.10 | 6.61 | 18,100 | |
| 3/4 | CB20SF | 2.40 | 2.09 | 0.91 | 1.02 | 2.01 | 2.05 | 0.94 | 7.20 | 12.57 | 28,300 | |
| 7/8 | CB22SF | 2.83 | 2.44 | 0.96 | 1.14 | 1.97 | 2.44 | 1.06 | 8.39 | 19.40 | 34,200 | |

CLEVIS GRAB HOOK WITH SADDLE

| For Chain Size | Part # | Dimensions (in) | | | | | | | Weight (lbs) | WLL (lbs) |
|----------------|--------|-----------------|------|------|------|------|------|-----------|--------------|-----------|
| | | A | B | C | G | H | R | PxL | | |
| 9/32-5/16 | CF08 | 0.39 | 0.35 | 0.39 | 1.18 | 0.94 | 1.97 | 0.35x0.89 | 0.60 | 4,500 |
| 3/8 | CF10 | 0.51 | 0.51 | 0.55 | 1.73 | 1.22 | 2.83 | 0.51x1.24 | 1.65 | 7,100 |
| 1/2 | CF13 | 0.67 | 0.67 | 0.67 | 2.09 | 1.50 | 3.46 | 0.63x1.65 | 2.98 | 12,000 |
| 5/8 | CF16 | 0.79 | 0.83 | 0.79 | 2.52 | 2.36 | 4.37 | 0.83x2.03 | 6.17 | 18,100 |
| 3/4 | CF20 | 0.94 | 0.94 | 0.94 | 3.35 | 2.56 | 5.12 | 0.94x2.42 | 10.58 | 28,300 |
| 7/8 | CF22 | 1.02 | 1.02 | 1.02 | 3.43 | 2.68 | 5.47 | 1.02x2.83 | 12.46 | 34,200 |