

# MULTI-PAK™ Large Cylinder Air Carts



**MULTI-PAK™**  
Large Cylinder Air Cart  
MP-2300HNB



**MULTI-PAK™**  
Large Cylinder Air Cart  
MP-2300ENB



**MULTI-PAK™**  
Cart Cover  
MP-2300C

## Large Cylinder Air Carts - Cylinder Pressures 2,400 PSI to 5,000 PSI

The MULTI-PAK™ series of large air cylinder carts are designed for long duration industrial applications and built for mobility and function. The carts incorporate protected recessed controls, equipment storage boxes, a narrow profile for maneuverability, 16" pneumatic tires, and quick-release hose hangers.

### Key Details:

- Universal hand tight nuts (CGA-347) - fits 2,400 to 5,000 psi cylinders
- Solid aluminum block manifold
- High flow adjustable regulator
- Input and output pressure gauges
- Steel storage box with latch
- Quick release hose rack - holds 200 feet of 3/8" hose
- 16" pneumatic tires
- Dimensions: 62" H x 25" W x 30" D
- Cart Only weight: 112 lbs. no cylinders



Steel Rear Storage Box



Hose Storage Rack Holds 200 Feet of 3/8" Hose



### MULTI-PAK™ Large Air Cylinder Carts

Item No.	Description
MP-2300ENB	MULTI-PAK™ two cylinder air cart, 5,000 psi, <b>pneumatic alarm whistle</b> (bell alarm available) for Hazardous Locations. 112 lbs. with no cylinders.
MP-2300HNB	MULTI-PAK™ two cylinder air cart, 5,000 psi, <b>electronic alarm whistle</b> for Non-Hazardous Locations. 115 lbs. with no cylinders.
MP-2300C	Black nylon cart cover for 2300 series carts

**Cylinders Not Included**

### Air Storage Cylinders

Item No.	Description
AC-300	300 cf CGA-346, 2400 psi, steel, DOT/TC approved
AC-444	444 cf CGA-347, 4500 psi, steel, DOT/TC/ISO/UN approved
AC-472	472 cf CGA-347, 5000 psi, steel, DOT/TC/ISO/UN approved