

Specialty Hand Trucks

Cylinder/Gas Trucks



Single 330 Cu. Ft. Cylinder Truck

- Designed to handle 330 cu. ft. cylinder.
- Two rear casters provide added stability.
- Includes heavy-duty holding chain.
- Color: Yellow.

Model No.	Wheel Type	Wheel Size Inches	Wheel Size mm
RCTD40SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70
Base Plate - 14"W x 6"D (356 x 152mm)		OAH - 45"	1143



Single & Dual Gas Trucks

- Heavy-duty truck designed to handle 330 cu. ft. cylinders.
- Available in single and dual cylinder models.
- Includes heavy-duty holding chain.
- Hard rubber swivel caster.
- Color: Yellow.

Model No.	Description	Wheel Type	Wheel Size Inches	Wheel Size mm
RGTS10FP	Single	Full Pneumatic	10 x 3 ¹ / ₂	254 x 89
RGTD10FP	Dual	Full Pneumatic	10 x 3 ¹ / ₂	254 x 89
RGTS10SP	Single	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70
RGTD10SP	Dual	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70
Base Plate - 14"W x 6"D (356 x 152mm)			OAH - 45"	1143



Dual Cylinder Truck with T-Handle

- Handles cylinders in a medium-duty application.
- Priced economically with its T-handle design.
- Two heavy-duty holding chains and tool tray.
- Color: Yellow.

Model No.	Wheel Type	Wheel Size Inches	Wheel Size mm
RCT40LW	Lightweight	8 x 1 ³ / ₄	203 x 44
Base Plate - 17"W x 8"D (432 x 203mm)		OAH - 43"	1092



Single Cylinder Hand Truck

- Perfect for medium to large cylinders.
- Also transports boxes or other bulky items.
- Includes heavy-duty holding chain.
- Color: Yellow.

Model No.	Wheel Type	Wheel Size Inches	Wheel Size mm
RCTV40SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70
Base Plate - 14"W x 7"D (356 x 178mm)		OAH - 48"	1219



Dual Cylinder Truck with Dual Handle

- Carries cylinders in a medium-duty application.
- Welded tank holders.
- Two heavy-duty holding chains and tool tray.
- Dual handle with vinyl grips.
- Color: Yellow.

Model No.	Wheel Type	Wheel Size Inches	Wheel Size mm
RCT50SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70
Base Plate - 20"W x 9"D (508 x 229mm)		OAH - 45"	1143



Dual Cylinder Truck with Continuous Handle

- Heavy-duty truck accommodates most cylinder tanks.
- Includes heavy-duty holding chain and tool tray.
- Easily carries two 300 cu. ft. tanks.
- Color: Yellow.

Model No.	Wheel Type	Wheel Size Inches	Wheel Size mm
RCT30FP	Full Pneumatic	10 x 3 ¹ / ₂	254 x 89
RCT30SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70
Base Plate - 20"W x 11"D (508 x 279mm)		OAH - 39"	991