







# Section 1: Lubrication Fittings

General Information • Military Reference • 1/4"-28 Taper Thread • 1/4"-28 Straight Thread  
 1/8" PTF • 1/4" PTF • 1/4"-28 and 1/8" Thread Forming • Drive • Metric  
 British Standard Pipe Thread • Monel • Stainless Steel • Standard Button Head  
 Giant Button Head • Relief • Flush Type • Pin Type • Hydraulic Shut-Off • Leakproof  
 Vents • Breathers • Special Thread • Rivet • Assortments • Header Blocks

## 1/4"-28 and 1/8" Thread-Forming Fittings

Thread-forming fittings have special tapered drive threads to reshape the material in an untapped hole to provide a leakproof seal. They are most effectively installed by spinning into the untapped hole, but may be driven straight into the untapped hole. Thread-forming fittings can be replaced by any standard threaded fitting or by another thread-forming fitting.



### FEATURES:

- Provides leakproof seal
- Exceeds 72-hour salt-spray test
- Maximum pressure: 10,000 psi
- Highest torque rating of any comparable fitting

Product #	Thread	Type	Hex Size	Hole Size Recommended
3038-B	1/4"-28 Spl. Taper	Str.	5/16"	.230 - .235
3053-B	1/4"-28 Spl. Taper	45°	3/8"	.230 - .235
3054-B	1/4"-28 Spl. Taper	90°	3/8"	.230 - .235
1720-B	1/8" Spl. Taper	Str.	7/16"	.373 - .380
1724-B	1/8" Spl. Taper	45°	7/16"	.373 - .380
1722-B	1/8" Spl. Taper	65°	7/16"	.373 - .380
1723-B	1/8" Spl. Taper	90°	7/16"	.373 - .380
369584	1/4"-28 Spl. Taper	Str.	5/16"	.230 - .235
369582	1/4"-28 Spl. Taper	Str.	9/32"	.230 - .235
369600	1/4"-28 Spl. Taper	90°	3/8"	.230 - .235
369607	1/4"-28 Spl. Taper	Str.	5/16"	.230 - .235
369579	1/8"-27 Spl. Taper	Str.	7/16"	.373 - .380

### IMPORTANT INFORMATION

NOTE: Geometry modifications and alternate materials available on request. We offer trivalent plating per GMW3044.