

Pressurized Oil Dispenser


Alemite's Pressurized Oil Dispenser safely and conveniently delivers oils to engine crankcases, transmissions, and differentials and machine reservoirs with the use of air pressure.

Features

- Available metered or non-metered control valve
- 17-gallon (65 liter) tank
- 79-inch (200 cm) clear dispensing hose with valve
- Air pressure gauge
- Pressure relief valve
- Fluid level gauge
- Two manually operated shutoff ball valves
- Handy tool caddy
- Splash-less funnel
- Convenient push handle
- Wheel/caster design for portability and stability
- Available sticker kit for easy labeling

Benefits

- Economical method of dispensing fluids
- Makes vehicle and equipment servicing easier
- Self-contained design eliminates spills
- External pumping source not required
- Will not over pressurize





Markets/Applications

Industrial Facilities • Car Dealerships • Quick Lubes • Tire Stores • Garages

Compatible Fluids

Oils (Motor, Cutting, Gear, Hydraulic) • Windshield Wiper Fluid • Coolants • ATF



WARNING: Not for use with flammable or caustic fluids

Technical Specifications

Part numbers	8589 (with meter)	8589-A (without meter)
	English units	Metric units
Operating air pressure	45-120 psi	3-8 bar
Pressure relief valve	145 psi	10 bar
Oil capacity	13 gallons	50 liters
Approximate flow rate*	1.2 gallons/minute at 45 psi	4.5 liters/minute at 3 bar
	3.5 gallons/minute at 120 psi	13.2 liters/minute at 8 bar

*With SAE 10W40 oil and 3660 metered valve



167 Roweland Drive
Johnson City, TN 37601
Toll Free U.S.: 866-4-Alemite
Toll Free Canada: 800-267-8022
International: 803-802-0001
Fax U.S.: 800-648-3917
Fax Canada: 800-267-2880
Fax International: 803-802-0192
www.alemite.com