





EGH Eye Grab Hook with Saddle




Part #	Trade Size	WLL (lbs)	Weight (lbs)	Dimensions (in)					
				A	B	C	E	F	H
10EGH08	9/32-5/16	5,700	0.73	1.40	0.59	2.28	1.02	2.22	0.39
10EGH10	3/8	8,800	1.67	1.75	0.77	2.99	1.46	2.85	0.47
10EGH13	1/2	15,000	3.09	2.34	0.94	4.02	1.65	3.66	0.59
10EGH16	5/8	22,600	4.85	2.76	1.18	4.45	1.81	4.20	0.87
10EGH20	3/4	35,300	7.74	3.27	1.46	5.28	2.17	5.08	0.89
10EGH22	7/8	42,700	13.69	3.60	1.48	6.02	2.64	5.81	1.02

CWC Chain to Web Connecting Link




Part #	Chain Size Inches	WLL (lbs.)	Weight (lbs.)	Dimensions (in)							
				A	B	C	D	E	F	G	H
10CWC08	9/32-5/16	5,700	0.71	0.43	2.48	1.97	0.91	2.48	1.57	0.55	0.94
10CWC10	3/8	8,800	1.32	0.55	3.15	2.40	1.14	3.03	1.97	0.59	1.10
10CWC13	1/2	15,000	2.45	0.67	3.74	2.99	1.34	3.66	2.36	0.75	1.30
10CWC16	5/8	22,600	4.74	0.83	4.65	3.66	1.61	4.65	2.95	0.90	1.65

CFH Clevis Foundry Hook



Part#	Trade size	WLL (lbs)	Weight (lbs)	Dimensions (in)							
				C	D	E	F	G	H	J	
10CFH08	9/32-5/16	5,700	2.03	1.59	0.69	0.53	0.37	1.07	5.33	1.16	
10CFH10	3/8	8,800	4.15	1.85	0.75	0.61	0.49	1.32	6.19	1.42	
10CFH13	1/2	15,000	6.69	2.03	0.79	0.63	0.61	1.75	7.60	1.57	
10CFH16	5/8	22,600	11.20	2.97	1.18	1.06	0.73	2.20	8.73	1.85	

ISC In-Line Shortening Clutch



Part #	Trade size	WLL (lbs)	Weight (lbs)	Dimensions (in)									
				A	B	C	D	E	F	G	K	I	J
10ISC07	9/32	4,300	1.37	0.48	0.94	1.54	1.91	1.48	0.43	0.45	0.95	5.93	2.09
10ISC08	5/16	5,700	1.37	0.48	0.94	1.54	1.91	1.48	0.43	0.45	0.95	5.93	2.09
10ISC10	3/8	8,800	2.76	0.57	1.14	1.97	2.31	1.83	0.53	0.55	1.22	7.71	2.73
10ISC13	1/2	15,000	5.95	0.71	1.46	2.52	2.87	1.99	0.59	0.61	1.46	9.73	3.61
10ISC16	5/8	22,600	10.58	0.96	1.83	3.15	3.82	2.74	0.73	0.81	1.91	11.44	4.03