

# Netway<sup>®</sup> FIBER SOLUTIONS

SPECTRUM

## 8-Port Managed PoE+ Hardened Switches with Dual SFP (Fiber) Ports

### Features:

- UL Listed in the U.S. and Canada for Information Technology Equipment, CE Approved.
- Equipped with VLAN.
- Two (2) Gigabit SFP ports (uplink).
- Eight (8) ports up to 30W. Two (2) ports can be up to 60W (two (2) 10/100/1000 ports and six (6) 10/100 ports).
- Supports PoE (802.3af), PoE+ (802.3at) and Hi-PoE devices.
- Input: 48-56VDC.
- Units can be deployed with single or multi-mode fiber or composite cable which combines fiber with copper to simultaneously deliver power and data.
- Control, monitor and report power/diagnostics from anywhere over the network.

### Units with Power Supply/Charger:

- 115VAC/230VAC input.
- 115W max output.
- Built-in battery charger.
- Integral surge protection.



156

Model #	Configuration	Dimensions
NetWaySP8B	8-port switch board only	5.6"L x 4.5"W x 0.625"H
NetWaySP8PL	8-port PoE+ Hardened Switch on Backplane	10.75"H x 8.875"W x 2.375"D
NetWaySP8WPN	Outdoor 8-port Hardened Switch only in NEMA4/4X, IP66-11 enclosure	13.31"H x 11.31"W x 5.59"D
NetWaySP8WPP	Outdoor 8-port PoE+ Hardened Switch in NEMA4/4X, IP66-11 enclosure	13.31"H x 11.31"W x 5.59"D
NetWaySP8WPX	Outdoor 8-port PoE+ Hardened Switch in larger NEMA4/4X, IP66-11 enclosure, which accommodates four (4) 12VDC/4AH batteries (48V of backup).	17.53"H x 15.3"W x 6.67"D
NetWaySP8X	Indoor 8-port PoE+ Hardened Switch	13.5"H x 13"W x 3.25"D