

#13154 #13155 55-100 TON LOAD LOCK'R ALUMINUM JACKS

- Aluminum lock nut provides mechanical load holding for extended periods
- Composite bearings increase cylinder life and side load resistance
- Equipped with bolt-on hardened steel saddle
- Hard coat finish resists damage and extends cylinder life

Model	Capacity	Stroke	Min. Height	Max. Height	Weight
13154	55 tons	6" (15 cm)	13.2" (33.5 cm)	19.1" (48.5 cm)	26.2 lbs (11.9 kg)
13155	100 tons	6" (15 cm)	15.6" (39.6 cm)	21.5" (54 cm)	58 lbs (26 kg)



ACCESSORIES FOR ALUMINUM JACKS

#13122 SHUT OFF VALVE ASSEMBLY

- Allows pump to be removed while ram is extended
- For use with single acting hydraulic cylinder
- Rated at 10,000 PSI (700 BAR)



#13121-SBK SBK-SADDLE BASE CONVERSION KIT

- Reduces point loading of the saddle
- Recessed base plate reduces broken bolts
- No more bent/broken corners
- More stable lifting platform
- Upgrade your existing 55 ton jack
- Works on models #13120 and #13140

