



CDX Eye Grab Hook with Saddle




Dimensions (In)										
For Chain Size	Part #	A	D	G	H	O	R	M	Weight (lbs)	WLL (lbs)
7/32-1/4	CDX 06	0.31	0.33	0.87	0.87	0.53	2.11	1.40	0.40	3,000
9/32-5/16	CDX 08	0.39	0.43	1.18	1.10	0.67	2.76	1.85	0.88	5,700
3/8	CDX 10	0.51	0.59	1.73	1.34	0.87	3.41	2.17	1.94	8,800
1/2	CDX 13	0.67	0.71	2.09	1.85	1.02	4.35	3.19	4.30	15,000
5/8	CDX 16	0.75	0.83	2.52	2.36	1.26	5.08	3.62	7.05	22,600
3/4	CDX 20	0.93	0.91	3.35	2.52	1.50	6.04	3.94	10.8	35,300
7/8	CDX 22	1.02	1.18	3.43	2.80	1.65	7.24	4.53	16.53	42,700
1	CDX 26	1.20	1.42	3.94	3.54	2.17	8.39	5.00	28.66	59,700
1 1/4	CDX 32	1.52	1.73	6.30	4.41	2.32	9.65	7.87	67.24	90,400

CRGX Swivel Self Locking Hook



Dimensions (In)											
For Chain Size	Part #	R	A	B	O	D	G	H	T	Weight (lbs)	WLL (lbs)
7/32-1/4	CRGX 06	6.22	1.10	0.91	1.42	0.51	0.63	0.83	1.38	1.32	3,000
9/32-5/16	CRGX 08	7.17	1.34	1.06	1.42	0.51	0.79	1.02	1.69	2.43	5,700
3/8	CRGX 10	8.54	1.77	1.38	1.65	0.63	0.98	1.18	2.20	4.41	8,800
1/2	CRGX 13	10.67	2.13	1.69	1.97	0.83	1.38	1.57	2.72	8.82	15,000
5/8	CRGX 16	12.60	2.44	2.28	2.44	0.94	1.50	1.97	3.15	14.99	22,600

CJ Alloy Hooks for Synthetic Slings



Dimensions (In)											
Part#	Color	A	B	C	D	G	H	P	T	Weight (lbs)	WLL (lbs)
CJ026	Purple	3.07	4.84	0.47	1.61	0.67	0.79	0.63	1.22	1.54	2,600
CJ053	Green	3.58	5.83	0.75	1.77	0.83	1.02	0.67	1.57	2.65	5,300
CJ084	Yellow	4.45	6.89	0.83	2.17	0.98	1.26	0.98	1.97	4.85	8,400
CJ132	Red	5.21	8.78	1.57	2.76	1.42	2.34	1.42	2.34	9.90	13,200
CJ08T8	Blue	7.28	12.48	1.97	3.94	1.77	2.48	2.17	3.15	27.5	21,200

