



CLX Connecting Link




For Chain Size	Part #	Dimensions (in)						Weight (lbs)	WLL (lbs)
		A	C	O	R	P	S		
7/32-1/4	CLX 06	0.55	0.71	0.71	1.77	0.31	0.30	0.15	3,000
9/32	CLX 07	0.70	0.79	0.81	1.99	0.40	0.35	0.31	4,300
5/16	CLX 08	0.75	1.00	0.93	2.44	0.45	0.39	0.44	5,700
3/8	CLX 10	0.94	1.18	1.08	2.83	0.50	0.50	0.77	8,800
1/2	CLX 13	1.10	1.42	1.31	3.44	0.75	0.66	1.63	15,000
5/8	CLX 16	1.35	1.59	1.56	4.13	0.81	0.81	2.56	22,600
3/4	CLX 20	1.65	1.81	1.81	4.45	1.14	0.98	5.51	35,300
7/8	CLX 22	1.93	2.17	2.28	5.24	1.18	1.10	6.83	42,700
1	CLX 26	2.24	3.35	2.76	7.56	1.57	1.18	14.99	59,700
1-1/4	CLX 32	3.15	3.33	3.70	8.11	1.85	1.38	25.35	90,400

CBX Clevis Sling Hook with Forged Latch



For Chain Size	Part #	Dimensions (in)									Weight (lbs)	WLL (lbs)
		A	A1	B	C	G	H	R	PXL			
7/32-1/4	CBX 06SF	1.02	0.75	0.28	0.31	0.59	0.79	2.72	0.3 X 0.69	0.55	3,000	
9/32	CBX 07SF	1.34	1.02	0.37	0.39	0.75	1.10	3.74	0.35 X 0.89	1.10	4,300	
5/16	CBX 08SF	1.34	1.02	0.37	0.39	0.75	1.10	3.74	0.39 X 0.89	1.10	5,700	
3/8	CBX 10SF	1.57	1.22	0.47	0.53	0.98	1.30	4.33	0.51 X 1.16	2.20	8,800	
1/2	CBX 13SF	2.01	1.57	0.59	0.67	1.18	1.57	5.35	0.63 X 1.46	3.75	15,000	
5/8	CBX 16SF	2.20	1.77	0.71	0.87	1.46	1.89	6.10	0.79 X 2.05	7.05	22,600	
3/4	CBX 20SF	2.36	2.09	0.91	1.02	2.01	2.05	7.28	0.94 X 2.87	11.02	35,300	
7/8	CBX 22SF	2.76	2.44	0.98	1.14	1.97	2.48	8.27	1.02 X 2.83	27.12	42,700	

CFX Clevis Grab Hook with Saddle



For Chain Size	Part #	Dimensions (in)									Weight (lbs)	WLL (lbs)
		A	B	C	G	H	R	M	PXL			
7/32-1/4	CFX 06	0.31	0.31	0.35	0.87	0.87	2.03	1.40	0.30 X 0.69	0.44	3,000	
9/32	CFX 07	0.39	0.39	0.45	1.18	1.10	2.62	1.85	0.35 X 0.89	0.97	4,300	
5/16	CFX 08	0.39	0.39	0.43	1.18	1.10	2.60	1.85	0.39 X 0.89	0.97	5,700	
3/8	CFX 10	0.51	0.51	0.59	1.73	1.34	3.15	2.17	0.51 X 1.24	2.12	8,800	
1/2	CFX 13	0.67	0.67	0.69	2.09	1.85	4.15	3.19	0.63 X 1.65	4.63	15,000	
5/8	CFX 16	0.75	0.75	0.72	2.52	2.36	4.40	3.62	0.83 X 2.03	7.50	22,600	
3/4	CFX 20	0.93	0.91	0.87	3.35	2.56	4.65	3.94	0.94 X 2.42	11.46	35,300	
7/8	CFX 22	1.02	1.02	0.98	3.62	2.68	6.06	4.72	1.02 X 2.83	17.20	42,700	