



AIR BAG 12

Featuring a 12" metal blower system with 15' or 25' ducting built into a heavy-duty polyester bag forming an all-in-one unit for ease of operation. Polypropylene nine-blade fan, steel/powder-coated housing and grill, carry handle with molded-in 2-speed switch.

- ▷ 60 Hz, 3.8 Amps, 2-speed On/Off switch
- ▷ Ducting: Single-Ply lightweight vinyl/polyester PVC-coated
- ▷ Yellow with black wear-strip and integrated nylon attachment strap on one end
- ▷ Dimensions: 28"l x 16"w x 14"h

AC MODEL

Free Air 1840 CFM
(high speed) 1/2 hp 120V AC, 60 Hz

Description	Order No.
AC with 15' Ducting - 35 lbs.	9535-12
AC with 25' Ducting - 41 lbs.	9535-12L

DC MODEL

Free Air 1360 CFM
(high speed) 1/2 hp 12V DC

Description	Order No.
DC with 15' Ducting - 36 lbs.	9535-12DC
DC with 25' Ducting - 39 lbs.	9535-12LDC

8" AND 12" AIR BAG BLOWER SYSTEMS WITH MVP

The complete Ventilation System includes everything you'll need for your confined space site. Systems include:

- ▷ 8" or 12" Metal all-in-one Air Bag Blower
- ▷ 15' of ducting
- ▷ Storage Bag
- ▷ 8" or 12" Manhole Ventilation Passthru (MVP)

Description	Order No.
8" AC Air Bag Blower System with 8" MVP	9520-358M
12" AC Air Bag Blower System with 12" MVP	9520-3512M



Video available on the ALLEGRO INDUSTRIES Channel
www.youtube.com/AllegroIndustries

