



AC HYDRAULIC AIR/HYDRAULIC JACKS



AC Hydraulic^{A/S}
NO COMPROMISE



AME International presents AC Hydraulic^{A/S} Air Hydraulic Jacks, designed for heavy-duty, intensive commercial use.

Hard chromium plated piston rod for long life. Built-in safety overload valve. Hand-operated dead-man's control for optimum safety while lifting and lowering. Portable air hydraulic jack also available, ideal for service vans, etc. Handy design - no loose tubes, handles, or valves. All air hydraulic jacks have an air supply of 130 - 174 psi and an air consumption of 350 l/min. Air hydraulic jacks have a handle length of 53.35" (135.5 cm). Portable air hydraulic jack (B25-2) handle length: 21.65" (55 cm).



10 YEAR
3 YEAR
UNLIMITED
WARRANTY

| Model | Capacity | Min. Height | Max. Height | Total Width | Frame Length | Weight | Included Extensions |
|-------|-------------------|---------------|--|----------------|-----------------|-------------------|-----------------------|
| B25-2 | 25 / 10 tons | 6.3" (16 cm) | 9.3" / 12.6" (23.5 / 32 cm) | 11.4" (29 cm) | 21.1" (53.5 cm) | 61.7 lbs (28 kg) | 2" / 3.9" (5 / 10 cm) |
| 25-1 | 25 tons | 8.7" (22 cm) | 13.6" (34.5 cm) | 12 (30.5 cm) | 30.3 (77 cm) | 136.7 lbs (62 kg) | 2" / 3.9" (5 / 10 cm) |
| 25-1H | 25 tons | 14.2" (36 cm) | 24" (61 cm) | 12.2 (31 cm) | 32.3 (82 cm) | 156.5 lbs (71 kg) | 2" / 3.9" (5 / 10 cm) |
| 25-2 | 25 / 10 tons | 7.1 (18 cm) | 10.8" / 15" (27.5 cm / 38 cm) | 12 (30.5 cm) | 30.3 (77 cm) | 132.3 lbs (60 kg) | 2" / 3.9" (5 / 10 cm) |
| 50-2 | 50 / 25 tons | 8.7" (22 cm) | 13.4" / 17.7" (34 cm / 45 cm) | 12.4 (31.5 cm) | 31.9 (81 cm) | 176.4 lbs (80 kg) | 2" / 3.9" (5 / 10 cm) |
| 50-3 | 50 / 25 / 10 tons | 5.9" (15 cm) | 8.3" / 10.4" / 13.2" (21 / 26.5 / 33.5 cm) | 12.2 (31 cm) | 31.9 (81 cm) | 147.7 lbs (67 kg) | 2" / 3.9" (5 / 10 cm) |



B25-2
Portable air hydraulic jack
Handy design - no loose tubes, handles, or valves.



Easy to operate – handle can be used for carrying, lifting, lowering, and maneuvering.

