

32 ESAB/L-TEC[®]

PLASMA

ESAB/L-TEC[®] PT-36 (M3[®])



Shield Retainer
37081



<u>Shield</u>	
0558007624	2.4mm 45-55A
0558009425	2.5mm 30-60A
0558006130	3.0mm 35-50A
0558006141	4.1mm 100-280A
0558006166	6.6mm 260-450A
0558006199	9.9mm 360-600A



<u>Diffuser</u>	
0004470030	(50A)
0004470031	(100-600A)
*0004470115	(100-600A CCW)
21944	(100-600A)
22496	(100-600A CCW)



Retaining Cap
37082



<u>Nozzle</u>	
0558006010ATTC	1.0mm (50A)
0558006014ATTC	1.4mm (100A)
0558006018ATTC	1.8mm (130A)
0558006020ATTC	2.0mm (200A)
0558006023ATTC	2.3mm (260/280A)
0558006025ATTC	2.5mm (280/300A)
0558006030ATTC	3.0mm (360A ALU)
0558006036ATTC	3.6mm (450A SS)
0558006041ATTC	4.1mm (600A SS)



<u>Electrode (silver) CleanCut</u>	
0558003914-AG	(50-450)
*0558005459ATTC	(low curr)
0558003928ATTC	(N2/H35)



<u>Gas Baffle</u>	
0558001625	(8 Hole) 300-600A
0558002530	(8 Hole rev.)
0558002533	(4 Hole) 100-280A
0558002534	(4 Hole rev.)



Contact Ring
37071



Electrode Holder
0558003924ATTC



Torch Body



Torch Receptacle