



AS 838     EG,  GR


**RH & LH SHELF BRACKET (RIGHT HAND SHOWN)**



A	B	C	Std. Pkg.	Wt./100 Pcs.
6"	2 <sup>15</sup> / <sub>16</sub> "	3"	25	56
8"	2 <sup>15</sup> / <sub>16</sub> "	5"	25	82
10"	2 <sup>15</sup> / <sub>16</sub> "	7"	25	112



A	B	C	Std. Pkg.	Wt./100 Pcs.
12"	3 <sup>7</sup> / <sub>16</sub> "	3"	25	134
14"	3 <sup>15</sup> / <sub>16</sub> "	4"	25	185
16"	4 <sup>7</sup> / <sub>16</sub> "	5"	20	198
18"	4 <sup>15</sup> / <sub>16</sub> "	6"	20	218
20"	5 <sup>7</sup> / <sub>16</sub> "	7"	20	258
22"	5 <sup>15</sup> / <sub>16</sub> "	8"	-	348



A	B	C	Std. Pkg.	Wt./100 Pcs.
24"	6 <sup>7</sup> / <sub>16</sub> "	5"	-	400
26"	6 <sup>15</sup> / <sub>16</sub> "	5 <sup>1</sup> / <sub>16</sub> "	-	445
28"	7 <sup>7</sup> / <sub>16</sub> "	6 <sup>9</sup> / <sub>16</sub> "	-	493
30"	7 <sup>15</sup> / <sub>16</sub> "	7"	-	545

Std Pkg & Wt./100 pcs: See chart above.

**LEGEND:**

**GR:** Powder Coated Supr-Green    **EG:** Electro-Galvanized    **PG:** Pre-Galvanized    **AL:** Aluminum    **HG:** Hot Dipped Galvanized    **PL:** Plain    **SS:** Stainless Steel    **ZTC:** Zinc Trivalent Chromium  
Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			