


AS 2631, AS 2631D

SWING GATE FIXTURE HANGER

Maximum design load is 120 lbs.
Safety factor of 3.



Catalog No.	For Use With	UL LISTED	Wt./ 100 Pcs.
AS 2631	AS 200	UL	25
AS 2631	AS 210, AS 300, AS 400, AS 500	-	25
AS 2631D	AS 100, AS 150, AS 200 BTB, AS 210 BTB	-	45



Snap Type Channel Hanger - Installation

Step 1:

The hanger is opened by releasing snap.




Step 2:

Channel is placed in the hanger & the snap cover is closed.




Step 3:



Snap Type Channel Hanger - Application Example

Threaded rod, hex nuts and washers are used to connect the hanger. The channel is installed as described above. A channel closure strip is required on the channel to create a wire raceway.

After the channel with closure strip is in place, the space between the closure strip and the top of the hanger allow removal of the strip for addition or removal of wire.



PROJECT INFORMATION

APPROVAL STAMP

Project:	<input type="checkbox"/> Approved
Address:	<input type="checkbox"/> Approved as noted
Contractor:	<input type="checkbox"/> Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	