

AS 815 EG

(6" TO 16" PIPE) DOUBLE ROLLER PIPE SUPPORT

Order Nuts and Bolts Separately.
For "A" Dimension Recommendations, see chart on next page.

Std Pkg: 5 Pr. · Wt/100 pcs: 680 lbs.

AS 1901 EG

(1/2" – 4" PIPE) PIPE ROLLER SUPPORT

For "A" Dimension Recommendations, see chart on next page.

Std Pkg: 10 Pr. · Wt/100 pcs: 125 lbs.

AS 1902 EG

(1" – 8" PIPE) PIPE ROLLER SUPPORT

Size	A	Wt/100 pcs
1"-2"	6 ³ / ₄	299
2 ¹ / ₂ "-3 ¹ / ₂ "	7 ¹ / ₂	304
4"-6"	8 ¹ / ₂	311
8"	9 ⁹ / ₁₆	319

For "A" Dimension Recommendations, see chart on next page.

Std Pkg & Wt/100 pcs: See chart above.

AS 1911 EG

(2" – 14" PIPE) PIPE ROLLER

Size	Std Pkg	Wt/100 pcs
2"-3 ¹ / ₂ "	25	160
4"-6"	20	215
8"-10"	-	525
12"-14"	-	1025

For "A" Dimension Recommendations, see chart on next page.

Std Pkg & Wt/100 pcs: See chart above.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium
Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

PROJECT INFORMATION		APPROVAL STAMP
Project:		<input type="checkbox"/> Approved
Address:		<input type="checkbox"/> Approved as noted
Contractor:		<input type="checkbox"/> Not approved
Engineer:		Remarks:
Submittal Date:		
Notes 1:		
Notes 2:		

AS 815 (6" - 16" PIPE) DOUBLE ROLLER PIPE SUPPORT

Order Nuts and Bolts Separately.




Chart for Dimension A							
Pipe Size	No Insulation	1"	1 1/2"	2"	2 1/2"	3"	4"
6"	9 1/2"	10 1/4"	10 1/2"	10 3/4"	11"	11 3/8"	11 7/8"
8"	10 1/8"		11"	11 3/8"	11 3/4"	12"	12 1/2"
10"	10 3/4"		11 5/8"	12"	12 1/4"	12 1/2"	13"
12"	11 1/4"		12 1/8"	12 1/2"	12 3/4"	13"	13 1/2"
14"	11 5/8"		12 1/2"	12 7/8"	13"	13 3/8"	14"
16"	12 1/8"		13"	13 3/8"	13 7/8"	14"	14 1/2"

AS 1901 (1 1/2" - 4" PIPE) PIPE ROLLER SUPPORT




Chart for Dimension A							
Pipe Size	No Insulation	1"	1 1/2"	2"	2 1/2"	3"	4"
1 1/2"	6 1/2"	6 1/2"					
3/4"	6 1/2"	6 1/2"	6 5/8"	6 7/8"			
1"	6 1/2"	6 1/2"	6 5/8"	6 7/8"			
1 1/4"	6 1/2"	6 1/2"	6 7/8"	7 1/8"	7 3/8"		
1 1/2"	6 1/2"	6 1/2"	6 7/8"	7 1/8"	7 3/8"		
2"	6 1/2"	6 5/8"	7 1/8"	7 3/8"	7 1/2"	8"	
2 1/2"	6 1/2"	6 5/8"	7 1/8"	7 3/8"	7 1/2"	8"	
3"	6 1/2"	7"	7 1/2"	7 3/4"	7 7/8"	8 1/8"	
3 1/2"	6 1/2"	7"	7 1/2"	7 3/4"	7 7/8"	8 1/8"	
4"	6 5/8"	7 1/4"	7 5/8"	7 7/8"	8"	8 3/8"	9

AS 1902 (1" - 8" PIPE) PIPE ROLLER SUPPORT




Chart for Dimension A	
AS 1902 Size	Dimension A
1" - 2"	6 3/4"
2 1/2" - 3 1/2"	7 1/2"
4" - 6"	8 1/2"
8"	9 9/16"

AS 1902 Size Selection							
Pipe Size	No Insulation	1"	1 1/2"	2"	2 1/2"	3"	4"
1 1/2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"			
3/4"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"			
1"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"			
1 1/4"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"			
1 1/2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"		
2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"		
2 1/2"	AS 1902-1"-2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"		
3"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-4"-6"	
3 1/2"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-4"-6"	
4"	AS 1902-1"-2"	AS 1902-2 1/2"-3 1/2"	AS 1902-2 1/2"-3 1/2"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-4"-6"	
5"	AS 1902-2 1/2"-3 1/2"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-8"	AS 1902-8"
6"	AS 1902-2 1/2"-3 1/2"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-4"-6"	AS 1902-8"	AS 1902-8"
8"	AS 1902-2 1/2"-3 1/2"	AS 1902-4"-6"	AS 1902-8"	AS 1902-8"	AS 1902-8"	AS 1902-8"	AS 1902-8"

AS 1911 PIPE ROLLER




Chart for Dimension A			
Size	Fit Pipe Size	A	B
2" - 3 1/2"	2"	5"	3"
	2 1/2"	5"	3 1/4"
	3"	5"	3 5/8"
4" - 6"	3 1/2"	5"	3 7/8"
	4"	5 7/8"	4 5/16"
	5"	5 7/8"	4 7/8"
8" - 10"	6"	5 7/8"	5 7/16"
	8"	8 5/16"	7 1/8"
	10"	8 5/16"	8 1/4"
12" - 14"	12"	10 7/8"	9 7/8"
	14"	10 7/8"	10 1/2"

NOTE: Anvil Strut Rollers Consist of Cast Iron Roller & Steel Bracket.