


AS 3281 EG

DOUBLE CONVEYOR ADJUSTING NUT




Use for all 1 5/8" wide Anvil-Strut channels. Size 3/8", Threads 16

Wt./100 pcs: 175 Lbs

AS 203 EG

LINKED EYELET WITH STUD




Size	Std Pkg	Wt/100 pcs
3/8"	100	27.0
1/2"	50	45.0

Max. Load: 610 lbs.

Std Pkg & Wt./100 pcs: See chart above.

AS 6075 EG

SLOTTED HEX HEAD MACHINE SCREW




Size	Std Pkg	Wt/100 pcs
1/4" x 3/4"	100	1.7
5/16" x 1"	100	2.6
5/16" x 1 1/4"	100	3.0
5/16" x 1 1/2"	100	3.4
3/8" x 1 1/4"	100	5.3

Std Pkg & Wt./100 pcs: See chart above.

AS 6024 EG

HEX HEAD CAP SCREW



Diameter	Length	Wt./100 Pcs.
1/4"	3/4"	1.3
1/4"	1"	1.7
1/4"	1 1/4"	2.0
1/4"	1 1/2"	2.0
3/8"	3/4"	4.0
3/8"	1"	4.5
3/8"	1 1/4"	5.3
3/8"	1 1/2"	6.1
3/8"	2"	7.6
1/2"	3/4"	8.0
1/2"	1"	9.1
1/2"	1 1/4"	10.0
1/2"	1 1/2"	11.6
1/2"	1 3/4"	13.2
1/2"	2"	14.7

For use with Channel Nuts to secure fittings to channels.

Std Pkg 100 & Wt./100 pcs: See chart above.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium
 Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			