

HBS-CE Extension Series PG, HG



HBS-CE-EXTENSION SERIES SUPPORT WITH THREADED ROD EXTENSION AND CHANNEL



HBS-CE-Extension Series is perfect for supporting natural gas and refrigeration piping systems, cable tray, electrical conduit, multiple lines, HVAC equipment and many other applications.

The HBS-CE-Extension is UV resistant and suitable for installation on most types of roofing material or other flat surfaces.

Roof supports come pre-assembled



Specifications – HBS-CE
Two H-Block Bases and Threaded Rod Riser with:
1 3/16" H-164 Channel, or 1 5/8" H-132 Channel
Material - 100% recycled rubber, UV resistant

HBS-CE-EXTENSION SERIES SUPPORT WITH THREADED ROD EXTENSION AND CHANNEL

Model No.	Height	Width	Strut Length	Strut Size	Base Length	Weight (Lbs)	Uniform Load Capacity (Lbs) *
<input type="checkbox"/> HBS-CE10-8-H-164-PG	8" (203mm)	5" (127mm)	9.312" (237mm)	1 3/16"	10 7/8" (276mm)	6.89	1,000*
<input type="checkbox"/> HBS-CE10-12-H-164-PG	12" (305mm)			H-164		7.34	1,000*
<input type="checkbox"/> HBS-CE24-16-H-132-PG	16" (406mm)		24.000" (610mm)	1 5/8" H-132	26" (660mm)	15.85	1,700*

* This load is only for the capacity of the components in this assembly. Please consult roofing manufacturer or engineer for roof load capacity

LEGEND:

PG: Pre-Galvanized HG: Hot Dipped Galvanized Pricing is located in the Anvil H-Block price book.

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			