

HBS-PH 48" Medium Duty Pipe Hanger Support PG, HG

HBS-PH 48" MEDIUM DUTY PIPE HANGER SUPPORT SERIES WITH TOP SUPPORT




The HBS-PH Series is designed specifically for supporting piping.

H-112
Channel
Shown



Specifications
Fixed Width & Height.
All hardware required for assembly is included.
Base Material - 100% recycled rubber, UV resistant
Crossbeams - 2⁷/₁₆" H-122 Channel or 3¹/₄" H-112 Channel



HBS-PH 48" MEDIUM DUTY PIPE HANGER SUPPORT SERIES WITH H-122 PG TOP SUPPORT

Model No.	Height	Strut Width	Base Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs) *
<input type="checkbox"/> HBS-PH-48-36-H-122-PG	48" (1219mm)	36" (914mm)	39 ³ / ₈ " (1000mm)	36" (914mm)	6	67	2,190*
<input type="checkbox"/> HBS-PH-48-48-H-122-PG		48" (1219mm)	51 ³ / ₈ " (1305mm)			70	1,635*
<input type="checkbox"/> HBS-PH-48-60-H-122-PG		60" (1524mm)	63 ³ / ₈ " (1610mm)			72	1,305*
<input type="checkbox"/> HBS-PH-48-72-H-122-PG		72" (1829mm)	75 ³ / ₈ " (1915mm)			75	1,080*

* This load is only for the capacity of the components in this assembly with the pipe hangers located at a distance ¹/₄ from each end of the top channel. For pipe hangers located ¹/₃ from each end, multiply uniform load by .75. For any other loading scenario, please consult the appropriate engineer. Please consult Roofing manufacturer or engineer for roof load capacity.
Torque Setting - All load capacities stated herein are based on the use of ¹/₂" channel nuts tightened to 50 ft-lbs.

HBS-PH 48" MEDIUM DUTY PIPE HANGER SUPPORT SERIES WITH H-112 PG TOP SUPPORT

Model No.	Height	Strut Width	Base Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs) *
<input type="checkbox"/> HBS-PH-48-36-H-112-PG	48" (1219mm)	36" (914mm)	39 ³ / ₈ " (1000mm)	36" (914mm)	6	69	3,505*
<input type="checkbox"/> HBS-PH-48-48-H-112-PG		48" (1219mm)	51 ³ / ₈ " (1305mm)			72	2,620*
<input type="checkbox"/> HBS-PH-48-60-H-112-PG		60" (1524mm)	63 ³ / ₈ " (1610mm)			75	2,090*
<input type="checkbox"/> HBS-PH-48-72-H-112-PG		72" (1829mm)	75 ³ / ₈ " (1915mm)			78	1,735*

* This load is only for the capacity of the components in this assembly with the pipe hangers located at a distance ¹/₄ from each end of the top channel. For pipe hangers located ¹/₃ from each end, multiply uniform load by .75. For any other loading scenario, please consult the appropriate engineer. Please consult Roofing manufacturer or engineer for roof load capacity.
Torque Setting - All load capacities stated herein are based on the use of ¹/₂" channel nuts tightened to 50 ft-lbs.

LEGEND:

PG: Pre-Galvanized **HG:** Hot Dipped Galvanized Pricing is located in the Anvil H-Block price book.

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			