


HBS-PH 48" Heavy Duty Pipe Hanger Support PG, HG

HBS-PH 48" HEAVY DUTY PIPE HANGER SUPPORT SERIES WITH TOP SUPPORT




The HBS-PH Series is designed specifically for supporting piping.

H-112A Channel Shown



Specifications
 Fixed Width & Height.
 All hardware required for assembly is included.
 Base Material - 100% recycled rubber, UV resistant
 Crossbeams - 4-7/8" H-122A Channel or 6-1/2" H-112A Channel



HBS-PH 48" HEAVY DUTY PIPE HANGER SUPPORT SERIES WITH H-122A PG TOP SUPPORT

Model No.	Height	Strut Width	Base Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs) *
<input type="checkbox"/> HBS-PH-48-36-H-122A-PG	48" (1219mm)	36" (914mm)	39 3/8" (1000mm)	36" (914mm)	6	74	3,870*
<input type="checkbox"/> HBS-PH-48-48-H-122A-PG		48" (1219mm)	51 3/8" (1305mm)			79	3,870*
<input type="checkbox"/> HBS-PH-48-60-H-122A-PG		60" (1524mm)	63 3/8" (1610mm)			83	3,845*
<input type="checkbox"/> HBS-PH-48-72-H-122A-PG		72" (1829mm)	75 3/8" (1915mm)			88	3,195*

* This load is only for the capacity of the components in this assembly with the pipe hangers located at a distance 1/4 from each end of the top channel. For pipe hangers located 1/3 from each end, multiply uniform load by .75. For any other loading scenario, please consult the appropriate engineer. Please consult Roofing manufacturer or engineer for roof load capacity. Torque Setting - All load capacities stated herein are based on the use of 1/2" channel nuts tightened to 50 ft-lbs.

HBS-PH 48" HEAVY DUTY PIPE HANGER SUPPORT SERIES WITH H-112A PG TOP SUPPORT

Model No.	Height	Strut Width	Base Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs) *
<input type="checkbox"/> HBS-PH-48-36-H-112A-PG	48" (1219mm)	36" (914mm)	39 3/8" (1000mm)	36" (914mm)	6	77	3,870*
<input type="checkbox"/> HBS-PH-48-48-H-112A-PG		48" (1219mm)	51 3/8" (1305mm)			82	3,870*
<input type="checkbox"/> HBS-PH-48-60-H-112A-PG		60" (1524mm)	63 3/8" (1610mm)			88	3,870*
<input type="checkbox"/> HBS-PH-48-72-H-112A-PG		72" (1829mm)	75 3/8" (1915mm)			94	3,870*

* This load is only for the capacity of the components in this assembly with the pipe hangers located at a distance 1/4 from each end of the top channel. For pipe hangers located 1/3 from each end, multiply uniform load by .75. For any other loading scenario, please consult the appropriate engineer. Please consult Roofing manufacturer or engineer for roof load capacity. Torque Setting - All load capacities stated herein are based on the use of 1/2" channel nuts tightened to 50 ft-lbs.

LEGEND:

PG: Pre-Galvanized **HG:** Hot Dipped Galvanized Pricing is located in the Anvil H-Block price book.

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			