

## HBS-Roller Series

PG,  HG


### HBS BASE WITH 1 5/8" H-132 PRE-GALV. STEEL CHANNEL AND ROLLERS



The HBS-Roller Series is designed for superior support of natural gas and refrigeration pipes. The roller allows for longitudinal movements of the pipe. This support is suitable for most types of roofing material or other flat surfaces.

Roof supports come pre-assembled

Specifications – HBS-Roller Series  
 H-Block Support with: 1 5/8" H-132 Channel  
 Material - 100% recycled rubber, UV resistant  
 Pipe O.D. - 1" thru 10"



### HBS BASE WITH 1 5/8" H-132 PRE-GALV. STEEL CHANNEL AND ROLLERS

Model No.	Pipe Size (O.D.)	Overall Height	Height to Roller Center	Strut Length	Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs) *
<input type="checkbox"/> HBS-R10-1-2-H-132-PG	1" to 2" (25 to 51mm)	8" (203mm)	7" (178mm)	9.312" (237mm)	5" (127mm)	10 7/8" (276mm)	1	9.13	1,500*
<input type="checkbox"/> HBS-R10-2-3 1/2-H-132-PG	2" to 3 1/2" (51 to 89mm)						1	8.94	1,500*
<input type="checkbox"/> HBS-R10-4-6-H-132-PG	4" to 6" (102 to 152mm)						1	9.37	1,500*
<input type="checkbox"/> HBS-R24-8-10-H-132-PG	8" to 10" (203 to 1254mm)	10 5/16" (262mm)	8 5/8" (219mm)			24" (610mm)	2	21.26	3,000*

\* This load is only for the capacity of the components in this assembly. Please consult roofing manufacturer or engineer for roof load capacity

#### LEGEND:

PG: Pre-Galvanized HG: Hot Dipped Galvanized Pricing is located in the Anvil H-Block price book.

PROJECT INFORMATION		APPROVAL STAMP
Project:		<input type="checkbox"/> Approved
Address:		<input type="checkbox"/> Approved as noted
Contractor:		<input type="checkbox"/> Not approved
Engineer:		Remarks:
Submittal Date:		
Notes 1:		
Notes 2:		