

## HBS-PH 36" Light Duty Pipe Hanger Support PG, HG


### HBS-PH 36" LIGHT DUTY PIPE HANGER SUPPORT SERIES WITH H-132 PG TOP SUPPORT



The HBS-PH Series is designed specifically for supporting piping.



**Specifications**  
 Fixed Width & Height.  
 All hardware required for assembly is included.  
 Base Material - 100% recycled rubber, UV resistant  
 Crossbeams - 1-5/8" H-132 Channel



### HBS-PH 36" LIGHT DUTY PIPE HANGER SUPPORT SERIES WITH H-132 PG TOP SUPPORT

Model No.	Height	Strut Width	Base Width	Base Length	No. of Bases	Weight (Lbs)	Uniform Load Capacity (Lbs) *
<input type="checkbox"/> HBS-PH-36-36-H-132-PG	36" (914mm)	36" (914mm)	39 3/8" (1000mm)	36" (914mm)	6	62	1,145*
<input type="checkbox"/> HBS-PH-36-48-H-132-PG		48" (1219mm)	51 3/8" (1305mm)			64	855*
<input type="checkbox"/> HBS-PH-36-60-H-132-PG		60" (1524mm)	63 3/8" (1610mm)			66	680*
<input type="checkbox"/> HBS-PH-36-72-H-132-PG		72" (1829mm)	75 3/8" (1915mm)			68	565*

\* This load is only for the capacity of the components in this assembly with the pipe hangers located at a distance 1/4 from each end of the top channel. For pipe hangers located 1/3 from each end, multiply uniform load by .75. For any other loading scenario, please consult the appropriate engineer. Please consult Roofing manufacturer or engineer for roof load capacity.  
 Torque Setting - All load capacities stated herein are based on the use of 1/2" channel nuts tightened to 50 ft-lbs.

**LEGEND:**

**PG:** Pre-Galvanized **HG:** Hot Dipped Galvanized Pricing is located in the Anvil H-Block price book.

PROJECT INFORMATION		APPROVAL STAMP
<b>Project:</b>		<input type="checkbox"/> Approved
<b>Address:</b>		<input type="checkbox"/> Approved as noted
<b>Contractor:</b>		<input type="checkbox"/> Not approved
<b>Engineer:</b>		<b>Remarks:</b>
<b>Submittal Date:</b>		
<b>Notes 1:</b>		
<b>Notes 2:</b>		