

HBM Series


PG

HBM-SUPPORT WITH STEEL CHANNEL



Specifications – HBM Series
 H-Block Mini Support with:
 $1\frac{3}{16}$ " H-164 Channel, or $1\frac{1}{8}$ " H-132 Channel
 Material - 100% recycled rubber, UV resistant


A cost-effective method for mounting and supporting single pipe applications without losing strength and integrity.



HBM-SUPPORT WITH $1\frac{3}{16}$ " H-164 PRE-GALV STEEL CHANNEL

Model No.	Height	Width	Base Length	Weight (Lbs)	Uniform Load Capacity (Lbs)*
<input type="checkbox"/> HBM-5-H-164-PG	$4\frac{13}{16}$ " (122mm)	5" (127mm)	$6\frac{5}{8}$ " (168mm)	2.90	400 *

* This load is only for the capacity of the components in this assembly. Please consult roofing manufacturer or engineer for roof load capacity



HBM-SUPPORT WITH $1\frac{5}{8}$ " H-132 PRE-GALV STEEL CHANNEL

Model No.	Height	Width	Base Length	Weight (Lbs)	Uniform Load Capacity (Lbs)*
<input type="checkbox"/> HBM-5-H-132-PG	$5\frac{5}{8}$ " (147mm)	5" (127mm)	$6\frac{5}{8}$ " (168mm)	3.40	400 *

* This load is only for the capacity of the components in this assembly. Please consult roofing manufacturer or engineer for roof load capacity

LEGEND:

PG: Pre-Galvanized HG: Hot Dipped Galvanized Pricing is located in the Anvil H-Block price book.

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			