


## HBM-CE5 Extension Series PG

### HBM-CE5-EXTENSION SERIES SUPPORT WITH THREADED ROD EXTENSION AND CHANNEL



Specifications – HBM-CE5 Extension Series  
 H-Block Mini Support and Threaded Rod Riser  
 with 1 5/8" H-132 Channel  
 Material - 100% recycled rubber, UV resistant

A cost-effective method for mounting and supporting single pipe applications without losing strength and integrity.



### HBM-CE5-EXTENSION SERIES SUPPORT WITH THREADED ROD EXTENSION AND 1 5/8" H-132 PRE-GALV STEEL CHANNEL

| Model No.                                       | Height                       | Width         | Base Length       | Weight (Lbs) | Uniform Load Capacity (Lbs)* |
|---|------------------------------|---------------|-------------------|--------------|------------------------------|
| <input type="checkbox"/> HBM-CE5-10-12-H-132-PG | 10" - 12"<br>(254mm - 305mm) | 5"<br>(127mm) | 6 5/8"<br>(168mm) | 4.00         | 175 *                        |

\* This load is only for the capacity of the components in this assembly. Please consult roofing manufacturer or engineer for roof load capacity

#### LEGEND:

PG: Pre-Galvanized HG: Hot Dipped Galvanized Pricing is located in the Anvil H-Block price book.

| PROJECT INFORMATION |  | APPROVAL STAMP                             |
|---------------------|--|--|
| Project:            |  | <input type="checkbox"/> Approved          |
| Address:            |  | <input type="checkbox"/> Approved as noted |
| Contractor:         |  | <input type="checkbox"/> Not approved      |
| Engineer:           |  | Remarks:                                   |
| Submittal Date:     |  |  |
| Notes 1:            |  |  |
| Notes 2:            |  |  |