

NOTE: This product is discontinued, and remaining inventory is limited.

Carbon Steel Ball Valve Fig. 2000BV-RP




Material Specifications

- 1. Body**
ASTM A105
- 2. Cap**
ASTM A105
- 3. Ball**
SS304/SS316
- 4. Stem**
SS304/SS316
- 5. Body Seat**
RPTFE
- 6. Cap Seat**
RPTFE
- 7. Packing**
PTFE
- 8. Handle**
SS201
- 9. Handle Sleeve**
PVC
- 10. Thrust Washer**
PTFE
- 11. Gland**
SS
- 12. Washer**
SS
- 13. Handle Nut**
A2-70

General Specifications

- Reduced Port
- Working Pressure:
1/4" - 2" 2000WOG
- 1 Piece Body
- Blow Out Proof Stem
- Threads Conform to
ASME B1.20.1 (NPT)
- NACE MR0175
- Locking Handle



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

NOTE: This product is discontinued, and remaining inventory is limited.

Carbon Steel Ball Valve Fig. 2000BV-RP




Fig. 2000BV-RP Dimensions

Nominal Size	Pressure	Dimensions				Approx. Wt. Ea.
		A	B	C	D	
In./mm	PSI/bar	In./mm	In./mm	In./mm	In./mm	Lbs./kg
1/4 8	2000 137.9	1 ¹¹ / ₁₆ 43	1 ³ / ₆₄ 5	1 ³ / ₃₂ 28	2 ⁷ / ₈ 73	0.22 0.10
3/8 10	2000 137.9	1 ⁵⁵ / ₆₄ 47	9/ ₃₂ 7	1 ¹⁷ / ₆₄ 32	3 ¹⁵ / ₆₄ 82	0.35 0.16
1/2 15	2000 137.9	2 ⁷ / ₁₆ 62	1 ¹ / ₃₂ 9	1 ⁵⁵ / ₆₄ 47	4 ³⁹ / ₆₄ 117	0.66 0.30
3/4 20	2000 137.9	2 ⁴⁹ / ₆₄ 70	3 ¹ / ₆₄ 12.5	2 ³ / ₆₄ 52	4 ³⁹ / ₆₄ 117	1.10 0.50
1 25	2000 137.9	3 ²⁵ / ₆₄ 86	1 ⁹ / ₃₂ 15	2 ⁹ / ₁₆ 65	5 ¹ / ₈ 130	2.20 1.00
1 1/4 32	2000 137.9	3 ⁴⁵ / ₆₄ 94	5 ¹ / ₆₄ 20	2 ⁶¹ / ₆₄ 75	5 ¹³ / ₆₄ 132	3.24 1.47
1 1/2 40	2000 137.9	4 ¹ / ₆₄ 102	6 ³ / ₆₄ 25	3 ⁵ / ₆₄ 78	6 ³ / ₁₆ 157	3.97 1.80
2 50	2000 137.9	4 ¹⁷ / ₃₂ 115	1 ¹⁷ / ₆₄ 32	3 ³⁵ / ₆₄ 90	6 ¹⁹ / ₆₄ 160	6.61 3.00



asc-es.com

Building connections that last™