

Fig. 95

C-Clamp with Locknut

Size Range: $\frac{3}{8}$ " and $\frac{1}{2}$ "

Material: Carbon Steel

Finish: Plain or Zinc Plated

Service: Designed for fastening flange of "W" and "M" beam. Bottom hole tapped to accommodate hanger rod.

Approvals: Complies with Federal Specification A-A-1192A (Type 23)

WW-H-171-E (Type 23), ANSI/MSS SP-69 and MSS SP-58 (Type 23).

UL Listed (Sizes $\frac{3}{8}$ ").

FM Approved (Sizes $\frac{3}{8}$ " - $\frac{1}{2}$ ").

Installation: Follow recommended set screw torque values per MSS-SP-69 (See table on page 288).

Ordering: Specify rod size, figure number, name and finish.

Note: If a retaining clip is desired, you may specify either Fig. 89X or Fig. 89. For length and other ordering information, refer to Fig. 89X and Fig. 89.




FIG. 95: DIMENSIONS (IN) • LOAD (LBS) • TORQUE (IN-LBS) • WEIGHT (LBS)								Rod Sized Retaining Clips	
Rod Size A	Set Screw Size	Torque Value	Max Load	B	C	D	Weight	Fig. 89	Fig. 89X
$\frac{3}{8}$	$\frac{3}{8}$	60	230	$\frac{3}{4}$	$2\frac{1}{4}$	$2\frac{3}{8}$	0.34	$\frac{3}{8}$	$\frac{3}{8}$
$\frac{1}{2}$	$\frac{1}{2}$	125	380				0.40		$\frac{1}{2}$