

Slotted Power Bits with Finder Sleeves



1/4" Hex Power Drive



Part No. Complete Assembly	Part No. Bit Only	Screw Size	Bit Length		Blade Thickness		Bit Body Diameter	
			In.	mm	In.	mm	In.	mm
NOL-320	320-LX	4F-5R	3 3/4	95	.036	.91	.193	4.90
L-320X	320-LX	5F-6R	3 3/4	95	.036	.91	.193	4.90
M-320X	320-MX	6F-8R	3 3/4	95	.038	.97	.241	6.12
P-320X	320-PX	8F-10R	3 3/4	95	.042	1.07	.290	7.37
R-320X	320-RX	10F-12R	3 3/4	95	.046	1.17	.350	8.89
S-320	320-S	12F-14R	3 7/8	98	.050	1.27	.395	10.03
T-320X	320-TX	14F-16R	4 1/8	105	.055	1.40	.457	11.61

1/4" Hex Power Drive – Extra Short Series



Part No. Complete Assembly	Part No. Bit Only	Screw Size	Bit Length		Blade Thickness		Bit Body Diameter	
			In.	mm	In.	mm	In.	mm
OOOL-322	322-000L	2F-3R	2 3/32	53	.026	.66	.138	3.91
OOL-322	322-00L	3F-4R	2 3/32	53	.030	.76	.154	3.91
OL-322	322-0L	4F-5R	2 5/32	55	.034	.86	.185	4.70
L-322	322-L	5F-6R	2 5/32	55	.036	.91	.185	4.70
M-322	322-M	6F-8R	2 5/32	55	.040	1.02	.248	6.30
P-322	322-P	8F-10R	2 5/32	55	.042	1.07	.283	7.19
R-322	322-R	10F-12R	2 5/32	55	.046	1.17	.283	7.19

1/4" Hex Power Drive – Long Series



Part No. Complete Assembly	Part No. Bit Only	Screw Size	Bit Length		Blade Thickness		Bit Body Diameter	
			In.	mm	In.	mm	In.	mm
L-328	328-L	5F-6R	6 1/2	165	.036	.91	.193	4.90
M-328	328-M	6F-8R	6 1/2	165	.038	.97	.241	6.12
P-328	328-P	8F-10R	6 1/2	165	.046	1.07	.290	7.37
R-328	328-R	10F-12R	6 1/2	165	.046	1.17	.350	8.89
S-328	328-S	12F-14R	6 1/2	165	.050	1.27	.395	10.03
T-328	328-T	14F-16R	6 1/2	165	.055	1.40	.457	11.61