



# Certification Record

The company named below has been authorized by CSA International to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

File Number: 112382\_0\_000

Status: ACT

Class Number: C337110

Submitter Name:

Aalberts Integrated Piping Systems Americas, Inc. DBA Conbraco Industries, Inc

0004514072

701 Matthews-Mint Hill Rd  
Matthews  
North Carolina  
28106  
United States

Factories:

Aalberts Integrated Piping Systems Americas, Inc. DBA Conbraco Industries, Inc

0004616920

125 Hwy 501 E  
Conway  
South Carolina  
29526  
United States

Contact ID: 0004514072

Aalberts Integrated Piping Systems Americas, Inc. DBA Conbraco Industries, Inc

701 Matthews-Mint Hill Rd

Matthews , North Carolina, 28106

United States

## Legacy File

December 14, 2020 (Replaces: June 26, 2017)

Model Number	Pressure Rating (psi)	Inlet Size	Outlet Size
89-101-01A, 489-101-01A	125	¼" NPT (F)	¼" NPT (F)
89-102-01A, 489-102-01A	125	3/8" NPT (F)	3/8" NPT (F)
89-103-01A, 489-103-01A	125	½" NPT (F)	½" NPT (F)
89-104-01A, 489-104-01A	125	¾" NPT (F)	¾" NPT (F)

89-105-01A, 489-105-01A	125	1" NPT (F)	1" NPT (F)
89-106-01, 489-106-01	125	1-1/4" NPT (F)	1-1/4" NPT (F)
89-107-01, 489-107-01	125	1-1/2" NPT (F)	1-1/2" NPT (F)
89-108-01, 489-108-01	125	2" NPT (F)	2" NPT (F)
89-109-01, 489-109-01	125	2-1/2" NPT (F)	2-1/2" NPT (F)
89-100-01, 489-100-01	125	3" NPT (F)	3" NPT (F)

1. Straight Through Carbon Steel Ball Type Lever Operated Non-Lubricated Manual Gas Shut-off Valve.
2. Mounting Position: Multipoise
3. Ambient Operating Temperature Range: -22°F to 149°F (-30°C to 65°C)

Model Number	Pressure Rating (psi)	Inlet Size	Outlet Size
76F-101-(01,27)	125	¼" NPT (F)	¼" NPT (F)
76F-102-(01,27)	125	3/8" NPT (F)	3/8" NPT (F)
76F-103-(01,27)A	125	½" NPT (F)	½" NPT (F)
76F-104-(01,27)A	125	¾" NPT (F)	¾" NPT (F)
76F-105-(01,27)A	125	1" NPT (F)	1" NPT (F)
76F-106-(01,27)A	125	1-1/4" NPT (F)	1-1/4" NPT (F)
76F-107-(01,27)A	125	1-1/2" NPT (F)	1-1/2" NPT (F)
76F-100-(01,27)A	125	3" NPT (F)	3" NPT (F)
76-101-01A	125	¼" NPT (F)	¼" NPT (F)
76-101-01A	125	¼" NPT (F)	¼" NPT (F)
76-102-01A	125	3/8" NPT (F)	3/8" NPT (F)
76-103-01A	125	½" NPT (F)	½" NPT (F)
76-104-01A	125	¾" NPT (F)	¾" NPT (F)
76-105-01A	125	1" NPT (F)	1" NPT (F)
76-106-01	125	1-1/4" NPT (F)	1-1/4" NPT (F)
76-107-01	125	1-1/2" NPT (F)	1-1/2" NPT (F)

76-108-01	125	2" NPT (F)	2" NPT (F)
76-109-01	125	2-1/2" NPT (F)	2-1/2" NPT (F)
76-100-01	125	3" NPT (F)	3" NPT (F)

1. Straight Through Stainless Steel Ball Type Lever Operated Non-Lubricated Manual Gas Shut-off Valve.
2. Mounting Position: Multipoise
3. Ambient Operating Temperature Range: -22°F to 149°F (-30°C to 65°C)

Model Number	Pressure Rating (psi)	Size
87A-203, 87A-903, 88A-203, 88A-903, 88L-203, 88L-903	125	1/2
87A-204, 87A-904, 88A-204, 88A-904, 88L-204, 88L-904	125	3/4
87A-205, 87A-905, 88A-205, 88A-905, 88L-205, 88L-905	125	1
87A-107, 87A-207, 87A-707, 87A-907, 88A-107, 88A-207, 88A-707, 88A-907, 88L-107, 88L-207, 88L-707, 88L-907	125	1 1/2
87A-108, 87A-208, 87A-708, 87A-908, 88A-108, 88A-208, 88A-708, 88A-908, 88L-108, 88L-208, 88L-708, 88L-908	125	2
87A-109, 87A-209, 87A-709, 87A-909, 88A-109, 88A-209, 88A-709, 88A-909, 88L-109, 88L-209, 88L-709, 88L-909	125	2 1/2
87A-100, 87A-200, 87A-700, 87A-900, 88A-100, 88A-200, 88A-700, 88A-900, 88L-100, 88L-200, 88L-700, 88L-900	125	3
87A-10A, 87A-20A, 87A-70A, 87A-90A, 88A-10A, 88A-20A, 88A-70A, 88A-90A, 88L-10L, 88L-20A, 88L-70A, 88L-90A	125	4
87A-10C, 87A-20C, 87A-70C, 87A-90C, 88A-10C, 88A-20C, 88A-70C, 88A-90C, 88L-10C, 88L-20C, 88L-70C, 88L-90C	125	6
87A-10E, 87A-70E, 88A-10E, 88A-70E, 88L-10E, 88L-70E	125	8

Description: 3-Piece Full Port Ball Valve

Trade Name: Apollo

Rated Pressure: 125 psi

<b>Model Numbers</b>	<b>Connection</b>	<b>Sizes</b>
83B-(141 to 148)	NPT Female	1/4", 3/8", 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83B-(241 to 248)	Socket-Weld	1/4", 3/8", 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83B-(343 to 348)	Butt-Weld, Schedule 5	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83B-(443 to 448)	Butt-Weld, Schedule 10	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83B-(543 to 548)	Butt-Weld, Schedule 40	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83B-(643 to 648)	Butt-Weld, Schedule 80	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
86B-(101 to 108)	NPT Female	1/4", 3/8", 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
86B-(201 to 208)	Socket-Weld	1/4", 3/8", 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
86B-(303 to 308)	Butt-Weld, Schedule 5	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
86B-(403 to 408)	Butt-Weld, Schedule 10	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
86B-(503 to 508)	Butt-Weld, Schedule 40	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
86B-(603 to 608)	Butt-Weld, Schedule 80	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83L-(141 to 148)	NPT Female	1/4", 3/8", 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83L-(241 to 248)	Socket-Weld	1/4", 3/8", 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83L-(343 to 348)	Butt-Weld, Schedule 5	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83L-(443 to 448)	Butt-Weld, Schedule 10	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"
83L-(543 to 548)	Butt-Weld, Schedule 40	1/2", 3/4", 1", 1-1/4", 1-1/2", 2"

83L-(643 to 648) Butt-Weld, Schedule 80 1/2", 3/4", 1", 1-1/4", 1-1/2", 2"

/jp