

NOTE: NOT ALL OPTIONS AND COMBINATIONS AVAILABLE ON ALL SIZES AND SERIES. REVIEW THE SPECIFIC TECHNICAL SHEET TO DETERMINE AVAILABILITY.

Modifying Suffixes

- The "01" suffix represents the standard configuration detailed in the Technical Literature.
- If an option is desired, replace the "01" suffix with the suffix of the option.
- If multiple options are desired, replace the "01" suffix with the desired suffixes in the order shown below.
Example: 87A-10A-1424MG

SIZE

OPTIONS

1	1/4"
2	3/8"
3	1/2"
4	3/4"
5	1"
6	1.25"
7	1.5"
8	2"
9	2.5"
0	3"
A	4"
C	6"
E	8"
G	10"
H	12"

-01	Standard Configuration
-02	Grounded
-04	2-1/4" Stem Extension
-05	Plain Ball
-07	Tee Handle
-08	90° Reversed Stem
-10	SS Lever and Fastener
-11	Therma-Seal™ Handle
-12	Stamped "157 SWP" & Bagged
-13	Stamped "157 SWP"
-14	Side Vented Ball (Uni-Directional)
-15	Round Handle, Steel
-16	Chain Lever - Valve in Vertical Position
-17	Rough Chrome Plated
-18	Plain Yellow Grip
-19	Pad-Locking
-20	Slot Vented Ball (Bi-Directional)
-21	UHMWPE Trim (Non PTFE)
-22	Viton Union Seals
-23	Tank Flange (2" 3-Pc. Valves Only)
-24	Graphite Packing (Not Always Firesafe)
-26	For Chlorine Service: Side Vented,Cleaned (CS, HC, Monel Only)
-27	SS Latch Lock Lever & Nut
-29	Graphite Packing & Seals (Firesafe)
-30	Cam-Lock Handle And Grounded
-31	7B Series w/Boss Not Drilled/Tapped
-32	SS Tee Handle & Nut (Hi-Rise Handle)
-33	73-300 Series w/Pad Drilled/Tapped
-34	Nylatron Seats (96 Series)
-35	PTFE (Virgin TFE)
-36	SS Hi-Rise Round Handle, SS Nut
-38	Peek Seats & Bearing, Graphite Packing & Seals
-39	SS Hi-Rise Locking Round Handle, SS Nut
-40	Cyl-Loc & Grounded
-41	Automatic Drain (Uni-Directional)
-42	Non-Vented Ball, No Hole in Slot (CS & SS)
-43	Cyl-Loc, Grounded Ball & Stem, 680 Loctite or 3 Tack Welds
-44	Seal Welded (76-100 & 89-100 Series)
-45	Less Lever & Nut (No Hangtag)
-46	Latch-Lock Lever - Lock in Closed Position Only
-47	SS Oval Latch-Lock Handle
-48	SS Oval Handle (No Latch)
-49	Assembled Dry
-50	2-1/4" Locking Stem Extension
-51	One Tack Weld
-52	Two Tack Welds
-53	Three Tack Welds
-54	Four Tack Welds
-56	Multifill Seats (MPTFE) Not Available When 250#SWP Applies
-57	Cleaned for Oxygen Service (N/A on LF Bronze with Solder Extensions)
-58	Chain Lever - Valve in Horizontal Position
-59	SS External Trim (3-Pc. and Flange Valves)
-60	Grounded Ball & Stem
-62	Body Center Section
-63	NPT x Solder / Socket Weld
-64	250# SWP (MPTFE Seats & Packing)
-65	MPTFE Seats & Graphite Packing (-24 & -56)
-66	FNPT x Butt Weld
-67	Cleaned for Industrial Gas (CS Valves) (I7361 Desiccant)
-69	Purge Ports (Drilled/Tapped at Bottom & Approx. 45°)
-70	4" Extended Bonnet
-72	RTFE Packing

-73	TFE Packing, Spiral Wound Body Seals, TFE Fillers
-75	MPTFE Seats, PTFE Packing, RPTFE Gaskets
-76	Live Loaded - with Lever
-77	Live Loaded - Actuated or Gear Operated
-78	Delrin Seats
-79	Nylon Seats - Graphite Packing (72 Series)
-8R	15% Glass Filled TFM 1600 Seats, PEEK Bearing
-80	Dyneon TFE 1600 Seats, PEEK Bearing
-81	Graphite Packing with Braided End Rings (Flange Valves)
-82	Flat Face Flanges
-83	SS Tee Handle & Nut (SS Version of -07) (77 Series)
-84	Reverse SS Lever & Nut (77B Series)
-85	Short SS Tee Handle & Nut (Silicone Bronze Retainer) (77B 1/2")
-86	Reverse Locking SS lever (77B Series) (Locking Version of -84)
-87	Safety Latch (Flange Valves)
-88	Panel Mount (60A Series)
-89	PFA Seats
-9P	Double Packed Extended Bonnet with Port
-90	Double Packed Extended Bonnet
-91	Latch-Lock Tee Handle, SS
-92	Balancing Stop
-94	-04 & Balancing Stop
-95	Devlon Seats, Graphite Packing, PEEK Bearing
-96	PCTFE Seats, Graphite Packing
-97	Ground, Round Handle, Pinned or Tack Welded
-99	For 7B Series: -99A Less Lever, Side Tap -99B Less Lever, No Tap
-AR	Actuator Ready (MPTFE Seats, Live Loaded, Less Lever)
-BC	Ball Check
-BK	PCTFE Bearing
-CE	CE Approved (1-1/4" and Above Only)
-DP	Dye Penetrate
-EF	Fugitive Emissions Packing (Graphite)
-EP	Garlock EVSP Packing, Graphite Spiral Wound Gasket
-GS	Gas Service; CSA Approved
-HC	3/4" Hose Thread Retainer with Brass Cap & Chain
-KF	Kel-F Bearing
-MG	Gear Operated, Standard Hand Wheel
-MH	Gear Operated, Standard Hand Wheel & Lockout Device
-MJ	Gear Operated, Oversize Hand Wheel
-MK	Gear Operated, Oversize Hand Wheel & Lockout Device
-MP	Material Positive (PMI Testing)
-PH	17-4 PH Stem
-RR	Oiled and Bagged for Rust Prevention on Carbon Steel Valves
-SR	Spring Return Handle (83A/B & 86A/B Series)
-SV	Safety Vent (77-100 / 7K-100 Series) (Auto Drain)
-SW	Limit Switch Mounted
-TC	Tested, Hydrostatic w/Certification
-TD	Tested to API 6D w/Certification
-TH	Tested, Hydrostatic
-TM	MTR
-TR	Tested, Hydrostatic w/Certification and MTR
-TS	Tested, Special, Customer Specified
-TW	Tested, Hydrostatic w/Witness and Certification
-UA	AIS Compliant
-US	Made in USA
-ZG	Cup & Cone Style Packing, Graphite
-ZP	Cup & Cone Style Packing, PTFE
-ZP1	Fugitive Emissions Packing (Viton)
-ZP2	Fugitive Emissions Packing (Buna-N)
-ZP3	Fugitive Emissions Packing (Kalrez)
-SP3	Corrosion Testing to ASTM A262 Practice A (SS Valves Only)