

SSH Flexible Fixture Hangers

Heavy Duty Outlet Box Swivel. Ball Joint Swivel Permits 20° Swing
UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.

NEC/CEC: Listed for Ordinary (Unclassified) Locations

LED Luminaires | Mounting Hangers | Ordinary Location | NEC / CEC

Applications

- Designed for suspension of lighting fixtures.
- SSH heavy duty swivel hangers for mounting to outlet and concrete boxes.

Features

- Protect fixture against wind and vibration damage.
- Heavy duty—support fixtures up to 22.7 kg (50 lbs).
- Steel plate serves as cover for outlet or concrete box.
- Ball type swivel joint permits 20° swing from vertical.

Standard Materials

- Malleable iron and steel

Standard Finishes

- Malleable iron and steel parts: zinc electroplate and clear chromate

NEC/CEC Certifications and Compliances

- CSA Certified: 065180
- UL Listed: E2527
- UL Standard: 514A



11360

APP11362

11355

Illustrated Features

Industrial lighting installations often employ the use of extra heavy fixtures requiring a properly anchored swivel attachment, assuring positive safety to carry the necessary weight. In the Type “SSH” Safety Swivel Hanger, the weight of the entire suspended unit is borne by a fixture stud instead of relying upon the screws and screw ears of the box or ring for support. The “SSH” hanger is furnished with a steel plate to serve as a cover for the 4” Concrete, Octagonal, and 4-11/16” Square boxes.

Cat. No. 11360 Safety Swivel Hanger installed in OCR3-1/2 Concrete Box with OCP3/8 Plate.





Cat. No. 11362 Safety Swivel Hanger installed in a 4-11/16” Square Box shown with NBFS-38 (not included).



SSH Flexible Fixture Hangers

Heavy Duty Outlet Box Swivel. Ball Joint Swivel Permits 20° Swing
UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.

NEC/CEC: Listed for Ordinary (Unclassified) Locations

	Support Weight in kg (lbs)	Fixture Stem Size (Inches)	Fixture Stud Size (Inches)	Weight in kg (lbs)	Catalog Number
Concrete Box — Safety Swivel Hanger — For Concrete Box 2-1/2" to 4" Deep					
	22.5 (50)	1/2	3/8	0.59 (1.30)	11360 ①
Octagonal Box — Safety Swivel Hanger — For 4" Octagonal Box 1-1/2" or 2-1/8" Deep					
	22.5 (50)	1/2	3/8	0.38 (0.83)	11355
Square Box — Safety Swivel Hanger — For 4-11/16" Square Box 1-1/2" or 2-1/8" Deep					
	22.5 (50)	1/2	3/8	0.59 (1.30)	APP11362

① Not CSA Certified.