

EMT Transition Couplings

Combination, Straight, 90°

NEC:
Listed for Ordinary Locations

Application

- Couplings are used to join lengths of steel EMT to various raceway systems.
- Connectors are used to secure and terminate steel EMT to knockouts and concrete tight box.

Features





- Compact design.
- No locknut required on the two piece connectors.
- Quick installations.

Material/Finish

- Steel/malleable iron - Zinc electroplated
- Zinc diecast - natural finish

NEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14895 (TWLL), E-14814 (TWCC)
- NEMA: FB-1

	Trade Size (Inches)	Dimensions in Millimeters (Inches)			Weight per 100 kg (lb)	Catalog Number	
		A	B	C			
Combination Couplings — EMT to Rigid Metal Conduit — Steel							
	1/2	17.5 (0.69)	12.7 (0.50)	25.4 (1.00)	4.54 (10.00)	TWR-50	
	3/4	17.5 (0.69)	13.5 (0.53)	32.5 (1.28)	6.80 (15.00)	TWR-75	
	1	22.4 (0.88)	13.5 (0.53)	40.4 (1.59)	7.71 (17.00)	TWR-100	
	1-1/4	24.6 (0.97)	21.3 (0.84)	49.3 (1.94)	18.14 (40.00)	TWR-125	
Connectors — Two Piece — Concrete Tight — Steel							
	1/2	7.9 (0.31)	8.6 (0.34)	26.9 (1.06)	2.72 (6.00)	92T050	
	3/4	7.9 (0.31)	11.2 (0.44)	32.5 (1.28)	3.99 (8.80)	92T075	
	1	8.6 (0.34)	10.4 (0.41)	41.4 (1.63)	5.90 (13.00)	92T100	
Combination Coupling — EMT to Flexible Metal Conduit — Zinc Diecast							
	1/2	32.5 (1.28)	31.8 (1.25)	23.9 (0.94)	3.40 (7.50)	TW38-50DC ①	
Combination Coupling — EMT to Flexible Metal Conduit — Malleable Body/Nut							
	1/2	21.3 (0.84)	16.0 (0.63)	26.9 (1.06)	5.44 (12.00)	TWCC38-50 ①	
	1/2	22.4 (0.88)	16.0 (0.63)	26.9 (1.06)	6.58 (14.50)	TWCC-50	
	3/4	26.9 (1.06)	16.8 (0.66)	33.3 (1.31)	11.34 (25.00)	TWCC-75	
	1	30.2 (1.19)	21.3 (0.84)	47.8 (1.88)	27.67 (61.00)	TWCC-100	

① Not UL Listed.