

# Armored Cable and Flexible Metal Conduit Connectors

NEC/CEC: — Listed for Ordinary Locations  
Suitable for use with flexible metal conduit in  
Class I, Division 2 Hazardous Locations per  
NEC 501.10 (B)(2)

## Flexible Metal Conduit Connectors One Screw and Two Screw

### Applications

- To ground and secure flexible metal conduit or armored cable to boxes and enclosures.

### Features

- Furnished with locknut.
- Male hub threads — NPS.
- Insulated throat version available.

### Standard Material/Finish

- Malleable iron/zinc electroplated

### NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-11853
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 009795
- NEMA: FB-1
- 7483/7483I – 7488/7488I CSA Certified for Armored Cable



7483



7483I




7485



7485I

### Illustrated Dimensions



Flexible Conduit Size (Inches)	Cable Opening in Millimeters (Inches)		Dimensions in Millimeters (Inches)			Catalog Number	Insulated Throat Catalog Number
	Max.	Min.	A	B	C		
<b>One Screw</b>							
1	35.1 (1.38)	26.2 (1.03)	28.7 (1.13)	12.7 (0.50)	50.0 (1.97)	7483	7483I
1-1/4	41.28 (1.63)	35.1 (1.38)	28.7 (1.13)	14.2 (0.56)	57.2 (2.25)	7484	7484I
<b>Two Screw</b>							
1-1/2	49.5 (1.95)	41.4 (1.63)	46.7 (1.84)	14.2 (0.56)	59.4 (2.34)	7485	7485I
2	62.2 (2.45)	54.9 (2.16)	50.8 (2.00)	19.1 (0.75)	84.1 (3.31)	7486	7486I
2-1/2	77.7 (3.06)	68.6 (2.70)	50.8 (2.00)	20.6 (0.81)	103.9 (4.09)	7487	7487I
3	90.4 (3.56)	77.0 (3.03)	55.6 (2.19)	23.9 (0.94)	115.8 (4.56)	7488	7488I
3-1/2	104.9 (4.13)	95.3 (3.75)	62.0 (2.44)	25.4 (1.00)	130.3 (5.13)	7489	7489I
4	118.6 (4.67)	106.4 (4.19)	68.3 (2.69)	25.4 (1.00)	144.5 (5.69)	7490	7490I