

ELS Series Emergency Lighting System

Explosionproof, Dust-Ignitionproof

Remote and direct mounted fixtures for hazardous location applications

NEC:

Class I, Division 1 and 2, Groups C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III

Emergency Lighting System Fixture for Remote Mounting — Lamp Included — Shown with Optional Guard

	Mounting Type	Watts Per Lamp	Lamp Voltage	Catalog Number (Lamp Included) ①
Pendant — One 1/2" Hub				
		18	6 Vdc	AP1050-186
		28	6 Vdc	AP1050-286
		18	12 Vdc	AP1050-1812
		28	12 Vdc	AP1050-2812
Ceiling — Four 1/2" Hubs, Three Close-Up Plugs				
		18	6 Vdc	AC1050-186
		28	6 Vdc	AC1050-286
		18	12 Vdc	AC1050-1812
		28	12 Vdc	AC1050-2812
Long Bracket — Four 1/2" Hubs, Three Close-Up Plugs				
		18	6 Vdc	ALB1050-186
		28	6 Vdc	ALB1050-286
		18	12 Vdc	ALB1050-1812
		28	12 Vdc	ALB1050-2812
Short Bracket — 15 degrees — Two 1/2" Hubs, One Close-Up Plug				
		18	6 Vdc	ASB1050-186
		28	6 Vdc	ASB1050-286
		18	12 Vdc	ASB1050-1812
		28	12 Vdc	ASB1050-2812
Emergency Lighting System Replacement Fixtures — Lamp included — Fits existing mounting hood				
		18	6 Vdc	AAU1N-186
		28	6 Vdc	AAU1N-286
		18	12 Vdc	AAU1N-1812
		28	12 Vdc	AAU1N-2812

① To order fixtures with guard installed, add suffix -G. Reflectors and exit signs are ordered separately. See Accessories page.