

AE Series Bolted Circuit Breakers and Enclosures

Explosionproof, Dust-Ignitionproof, Watertight

2- and 3-Pole, Non-Interchangeable Trip. Bolted Enclosure Type.

NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 4X

Application

- Explosionproof circuit breaker enclosures are used where hazardous materials are handled or stored.
- These units are used for overload and short circuit protection, control of lighting and power circuits.

Features

- Precision machined flame path between box and cover.
- Bolt on stainless steel slotted mounting feet.
- Stainless steel, captive Quad-Lead® cover bolts are standard (disengaged in 1-1/2 turns).
- Ground lug package and installation instructions for termination of ground wire enclosed.
- External operating handle with stops for limiting handle travel.
- Breaker operators can be locked in the ON or OFF position (up to 3 padlocks).
- External flange maximizes internal space.
- Standard outlets top and bottom for line and load wiring.
- Plugged 1/2" outlets top and bottom for breather and drain.
- Breakers mounted on a galvanized steel removable pan.
- Enclosures are designed to accept GE®, Square D®, Siemens+ and Cutler-Hammer † circuit breakers.
- O-ring gasket insures watertight integrity.
- 2- and 3-pole versions are standard. For 4-pole versions, contact your local representative.

Standard Materials

- Bodies and covers: copperfree (4/10 of 1% max.) aluminum
- Cover bolts, hinges, breaker and operator shafts: stainless steel
- Hinges: stainless steel
- O-ring: neoprene

Standard Finishes

- Bodies and covers: gray epoxy powder coat inside and outside standard

Options

Must be listed in alphanumeric sequence at the end of the catalog number.

- Auxiliary switch (1A or 1B), add suffix —**AS1**.
- Auxiliary switch (2A or 2B), add suffix —**AS2**.
- Breather, NEMA 4X (includes outlet and installation), add suffix —**BR**.
- Drain, NEMA 4X (includes outlet and installation), add suffix —**DN**.
- External grounding stud, add suffix —**EGS**.
- Plastic nameplate, 2" x 4", 1/8" black letters on white surface, 3 lines max, specify legend, add suffix —**NP**.
- Shunt trip (specify voltage), add suffix —**ST**.
- Under voltage release (specify voltage), add suffix —**UV**.
- For +50 °C (+122 °F) breaker rating, add suffix —**V**.
- For UL Listed Circuit Breakers with 65,000 AIC rating, contact your local sales representative.



NEC/CEC Certifications and Compliances

- UL Standard: UL 1203
- UL Classified: E84577
- CSA Standard: C22.2 No. 0, C22.2 No. 4, C22.2 No. 5, C22.2 No. 25, C22.2 No. 30
- CSA Certified (800A Max): 1324917

► GE is a registered trademark of General Electric Company.

■ Square D is a registered trademark of Schneider Electric.

† Cutler-Hammer is a registered trademark of Eaton Corporation.

★ Siemens is a registered trademark of Siemens AG.

AE Series Bolted Circuit Breakers and Enclosures

Explosionproof, Dust-Ignitionproof, Watertight

2- and 3-Pole, Non-Interchangeable Trip. Bolted Enclosure Type.

NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 4X

Catalog Numbering Guide

A
Appleton
AE Series

E
E - Explosionproof

A
Enclosure Size:
A - 15 - 50 AT
B - 60-100AT
C - 125-150AT
E - 175-225AT
F - 250-400AT
D - 400-600AT
L - 700-800AT
G - 1000-1200AT^①

B
Enclosure Type:
B - Bolted

1
Breaker Frame:
1 - 100-150AF
2 - 250AF
4 - 400AF
6 - 600AF
8 - 800AF
12 - 1200AF^①

3
Number of Poles:
3 - 3 Pole
4 - 4 Pole (Contact
your local
representative)^①

2
Line Voltage:
2 - 240
4 - 480
6 - 600

15
Breaker Trip:
15 - 15AT
20 - 20AT
25 - 25AT
30 - 30AT
35 - 35AT
40 - 40AT
50 - 50AT
60 - 60AT
70 - 70AT
80 - 80AT
90 - 90AT
10 - 100AT
12 - 125AT
15 - 150AT
17 - 175AT
20 - 200AT
22 - 225AT
25 - 250AT
30 - 300AT
35 - 350AT
40 - 400AT
45 - 450AT
50 - 500AT
60 - 600AT
70 - 700AT
80 - 800AT
10 - 1000AT^①
12 - 1200AT^①

C
Indicate Breaker
Manufacturer:
C - Cutler-Hammer
(standard)
S - Square D
G - GE
I - Siemens

▲
Suffix for Other
Options/Features:
Must be listed
in alphanumeric
sequence
(See Options)

DISTRIBUTION EQUIPMENT: NEC/CEC EXPLOSIONPROOF CIRCUIT BREAKERS

 **Appleton**

^① UL Classified. NEC Certification only.

▲ To complete the catalog number please add the appropriate suffix for other options/features. These suffixes can be found in the modifications table in this section.

AE Series Bolted Circuit Breakers and Enclosures

Explosionproof, Dust-Ignitionproof, Watertight

2- and 3-Pole, Non-Interchangeable Trip. Bolted Enclosure Type.

NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 4X

Circuit Breaker Interrupting Ratings (Symmetrical RMS Amps)

Breaker Type	240 Vac	480 Vac	600 Vac
Cutler-Hammer ⁺			
EHD	18,000	14,000	—
FD	65,000	35,000	18,000
HFD	100,000	65,000	25,000
JD	65,000	35,000	18,000
HJD	100,000	65,000	25,000
KD	65,000	35,000	25,000
HKD	100,000	65,000	35,000
LD	65,000	35,000	22,000
HLD	100,000	65,000	35,000
MDL	65,000	50,000	25,000
HMDL	100,000	65,000	35,000
ND	65,000	50,000	25,000
HND	100,000	65,000	35,000
GE [►]			
TED	18,000	18,000	14,000
THED	65,000	25,000	18,000
TFK	25,000	22,000	18,000
THFK	65,000	25,000	18,000
TJK4	42,000	30,000	22,000
THJK4	65,000	35,000	25,000
TJK6	42,000	30,000	22,000
THJK6	65,000	35,000	25,000
TKM8	42,000	30,000	22,000
THKM8	65,000	35,000	25,000
TKM12	42,000	30,000	22,000
THKM12	65,000	35,000	25,000

DISTRIBUTION EQUIPMENT: NEC/CEC EXPLOSIONPROOF CIRCUIT BREAKERS



► GE is a registered trademark of General Electric Company.

± Cutler-Hammer is a registered trademark of Eaton Corporation.

AE Series Bolted Circuit Breakers and Enclosures

Explosionproof, Dust-Ignitionproof, Watertight

2- and 3-Pole, Non-Interchangeable Trip. Bolted Enclosure Type.

NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 4X

Breaker Frame Size	Breaker Type/ Interrupting Capacity ①	Volts	Amp Rating	Catalog Numbers ② ▲		Standard Conduit Outlets (Inches)
				2-Pole	3-Pole	
100	EHD 18,000 AIC @ 240 Vac	480 Vac, 125/250 Vdc	15	AEAB12215C	AEAB13215C	1-1/2
			20	AEAB12220C	AEAB13220C	
			25	AEAB12225C	AEAB13225C	
			30	AEAB12230C	AEAB13230C	
			35	AEAB12235C	AEAB13235C	
			40	AEAB12240C	AEAB13240C	2
			50	AEAB12250C	AEAB13250C	
			60	AEBB12260C	AEBB13260C	
			70	AEBB12270C	AEBB13270C	
			80	AEBB12280C	AEBB13280C	
150	FD 65,000 AIC @ 240 Vac	600 Vac, 125/250 Vdc	90	AEBB12290C	AEBB13290C	2-1/2
			100	AEBB12210C	AEBB13210C	
			125	AECB12212C	AECB13212C	
			150	AECB12215C	AECB13215C	
			15	AEAB12415C	AEAB13415C	1-1/2
			20	AEAB12420C	AEAB13420C	
			25	AEAB12425C	AEAB13425C	
			30	AEAB12430C	AEAB13430C	
			35	AEAB12435C	AEAB13435C	
			40	AEAB12440C	AEAB13440C	2
100	EHD 14,000 AIC @ 480 Vac	480 Vac, 125/250 Vdc	50	AEAB12450C	AEAB13450C	
			60	AEBB12460C	AEBB13460C	
			70	AEBB12470C	AEBB13470C	
			80	AEBB12480C	AEBB13480C	
			90	AEBB12490C	AEBB13490C	
			100	AEBB12410C	AEBB13410C	2-1/2
			125	AECB12412C	AECB13412C	
			150	AECB12415C	AECB13415C	
			15	AEAB12615C	AEAB13615C	1-1/2
			20	AEAB12620C	AEAB13620C	
150	FD 35,000 AIC @ 480 Vac	600 Vac, 125/250 Vdc	25	AEAB12625C	AEAB13625C	
			30	AEAB12630C	AEAB13630C	
			35	AEAB12635C	AEAB13635C	
			40	AEAB12640C	AEAB13640C	2
			50	AEAB12650C	AEAB13650C	
			60	AEBB12660C	AEBB13660C	
			70	AEBB12670C	AEBB13670C	
			80	AEBB12680C	AEBB13680C	
			90	AEBB12690C	AEBB13690C	2-1/2
			100	AEBB12610C	AEBB13610C	
			125	AECB12612C	AECB13612C	
			150	AECB12615C	AECB13615C	

① For higher interrupting capacities, contact your local representative.

② Cutler-Hammer breaker provided as standard. For GE breaker change **C** to **G**; For Square D breaker change **C** to **S**; For Siemens breaker change **C** to **I**.

▲ To complete the catalog number please add the appropriate suffix for other options/features. These suffixes can be found under Options.


AE Bolted Circuit Breaker Enclosure

Explosionproof, Dust-Ignitionproof, Watertight

2- and 3-Pole, Non-Interchangeable Trip. Bolted Enclosure Type.

NEC/CEC:
Class I, Division 1 and 2, Groups B, C, D
Class II, Division 1 and 2, Groups E, F, G
Class III
NEMA 4, 4X

Dimensions in Millimeters (Inches)



Enclosure Only

Enclosure Size	Catalog Number	Dia. Number	Dimensions in Millimeters (Inches)									Number of Outlets	Dimension mm (in) K	Approximate Weight kgs (lbs)
			Mounting			Inside			Outside					
			A	B	J	C	D	E	F	G	H			
A	AEAB	1	139.7 (5.50)	333.5 (13.13)	358.9 (14.13)	155.7 (6.13)	273.0 (10.75)	133.3 (5.25)	270.0 (10.63)	387.3 (15.25)	224.5 (8.84)	2	50.8 (2.00)	17.24 (38)
B	AEBB	1	152.4 (6.00)	457.2 (18.00)	782.6 (19.00)	165.1 (6.50)	406.4 (16.00)	139.7 (5.50)	279.4 (11.00)	520.7 (20.50)	227.8 (8.97)	2	58.6 (2.31)	25.85 (57)
C	AECB	1	260.3 (10.25)	574.8 (22.63)	Not Available	289.0 (11.38)	508.0 (20.00)	162.0 (6.38)	406.4 (16.00)	638.3 (25.13)	243.5 (9.59)	2	88.9 (3.50)	47.17 (104)
E	AEEB	1	215.9 (8.50)	689.1 (27.13)	Not Available	285.7 (11.25)	758.9 (29.88)	183.8 (7.63)	406.4 (16.00)	749.3 (29.50)	311.9 (12.28)	2	101.6 (4.00)	65.77 (145)
F	AEFB-250	1	241.3 (9.50)	692.1 (27.25)	Not Available	285.7 (11.25)	758.9 (29.88)	204.7 (8.06)	416.0 (16.38)	889.0 (35.00)	313.4 (12.34)	2	106.4 (4.19)	77.11 (170)
F	AEFB-400	2	241.3 (9.50)	692.1 (27.25)	Not Available	285.7 (11.25)	758.9 (29.88)	204.7 (8.06)	416.0 (16.38)	889.0 (35.00)	320.8 (12.63)	2	106.4 (4.19)	77.11 (170)
D	AEDB	2	409.7 (16.13)	1035.0 (40.75)	Not Available	457.2 (18.00)	1079.5 (42.50)	193.8 (7.63)	346.2 (13.63)	962.1 (37.88)	325.3 (12.81)	2	109.4 (4.31)	103.42 (228)
L	AELB	3	406.4 (16.00)	1152.6 (45.38)	Not Available	473.2 (18.63)	1073.1 (42.25)	215.9 (8.50)	606.5 (23.88)	1216.1 (47.88)	361.9 (14.25)	4	127.0 (5.00)	190.06 (419)
G①	AEGB	4	543.1 (21.38)	1270.0 (50.00)	Not Available	508.0 (20.00)	1524.0 (60.00)	254.0 (10.00)	635.0 (25.00)	1651 (65.00)	534.0 (21.38)	6	111.2 (4.38)	257.19 (567)

① UL Classified. NEC Certification only.