

ACSEW Control Operators: Selector Switch Components


Explosionproof

NEC/CEC:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

NEC/CEC – cULus Optional:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

ATEX/IECEX – Optional ①:
 Zone 1 and 2 – 21 and 22
 II 2 GD
 IP66 – IK10

Catalog Numbering Guide



Two Position – Maintained Contact

Contact	Lever Position X=Closed, O=Open		Catalog Number		Contact Block Position		
	Left	Right	Standard Bushing	Long Bushing	L	R	Cam Location
1	O	X	AESS22MG	AESS22MG-L	NO	-	2
1	X	O	AESS22MH	AESS22MH-L	-	NO	2
1	O	X	AESS22ML	AESS22ML-L	NO	NO	2
2	X	O					
1	O	X	AESS22MM	AESS22MM-L	NO	NC	2
2	O	X					
1	X	O					
2	O	X	AESS22MR	AESS22MR-L	2NC	2NC	2
3	X	O					
4	O	X					

① Ordering a product with any ATEX Certification nulls the UL, CSA and cULus Certifications.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875").
 For legend plates, see Options, Accessories and Nameplates. All Operators are 3/4" NPSM.