

# A-51™ Incandescent Factory Sealed Luminaires

## For Group C and D Locations. Explosionproof

Suitable for use in Wet Locations. UNILETS® for use with Threaded Metal Conduit.

Class I, Division 1 and 2, Groups C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III

Appleton®

INCANDESCENT/AREA: NEC/CEC EXPLOSIONPROOF

Type	Hub Size (Inches)	Catalog Number ②		
<b>Long Bracket — Four Hubs, Three Close-up Plugs</b>				
	60-100 W (AAU-1N) A-21	1/2 3/4	ALB1050 ALB1075	
		1	ALB10100	
	150-300 W (AAU-15N) A-23 PS-25	1/2 3/4	ALB1550 ALB1575	
		1	ALB15100	
	200-300 W (AAU-2NS) PS-30	1/2 3/4	ALB2050 ALB2075	
		1	ALB20100	
	<b>15° Short Bracket — Two Hubs, One Close-up Plug</b>			
		60-100 W (AAU-1N) A-21	1/2 3/4	ASB1050 ASB1075
			1/2	ASB1550
150-300 W (AAU-15N) A-23 PS-25		3/4	ASB1575	
		1/2	ASB2050	
200-300 W (AAU-2NS) PS-30		3/4	ASB2075	
<b>Three-Way Exit Sign</b>				
	Epoxy enameled steel – 152.4 mm (6 in)-high red lettering 60-200 W (Mounts to AAU-1N or AAU-15N fixture units in place of guard)	CJEXRN		
<b>Single-Sided Exit Sign</b>				
	Epoxy enameled steel – 152.4 mm (6 in)-high red lettering 60-200 W (Mounts to AAU-1N or AAU-15N fixture units in place of guard) (See page G2-24 for dimensions)	AEXR-15R		
<b>Guard — Add suffix to fixture catalog number</b>				
	Guard	-G		

① See A-51™ Incandescent Factory Sealed Luminaire Classified Area Suitability page for suitability of specific fixtures.