

AL Ball and Cushion Flexible Fixture Hangers

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC. Ball Joint Permits 20° Swing.

NEC:

Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of HID, fluorescent and incandescent lighting fixtures.
- Functions as combination conduit outlet box and hanger.

Features

- Protects fixture against wind and vibration damage.
- Cushion type for added protection where lighting fixtures are subjected to vibration.
- Dual function—conduit outlet box and fixture hanger.
- Choice of ball or cushion type.
- Swivel joint construction—allows 20° swing from vertical.
- Cushion style, with conical spring, supports up to 54 kg (120 lbs).
- Cushion type has setscrew for locking fixture stem.
- Fixture and hanger stem can be wired at work bench.
- Connection block available for convenient wiring of fixture leads.

Standard Materials

- Malleable iron with steel cover

Standard Finishes

- Malleable iron parts: triple-coat—(1) zinc electroplate, (2) chromate, and (3) epoxy powder coat
- Steel parts: zinc electroplate

NEC Certifications and Compliances

- UL Listed: E109438



ALA — Ball Hanger



ALC — Ball Hanger




ALL — Cushion Hanger



ALT — Cushion Hanger

Illustrated Features



POLES/HANGERS: NEC/CEC ORDINARY LOCATION FLEXIBLE FIXTURE HANGERS



AL Ball and Cushion Flexible Fixture Hangers

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC. Ball Joint Permits 20° Swing.

NEC:
Listed for Ordinary (Unclassified) Locations

	Conduit Size (Inches)	Fixture Stem Size (Inches)	Support Weight kg (lbs)	Catalog Number
ALL – Ball Hanger				
	1/2	1/2	112.5 (250)	ALL50-B
	3/4	1/2		ALL7550-B
	3/4	3/4	112.5 (250)	ALL75-B
ALL – Cushion Hanger – Furnished with a 3/4" to 1/2" reducer for 1/2" stems				
	1/2	3/4 or 1/2	1.4 to 5.4 (3 to 12)	ALL50-12
	3/4	3/4 or 1/2		ALL7575-12
	1/2	3/4 or 1/2	5.4 to 21.6 (12 to 48)	ALL50-48
	3/4	3/4 or 1/2		ALL7575-48
	1/2	3/4 or 1/2	21.6 to 54 (48 to 120)	ALL50-120
	3/4	3/4 or 1/2		ALL7575-120
ALT – Ball Hanger				
	1/2	1/2	112.5 (250)	ALT50-B
	3/4	1/2		ALT7550-B
	1	1/2		ALT1050-B
	3/4	3/4	112.5 (250)	ALT75-B
	1	3/4	112.5 (250)	ALT1075-B
ALT – Cushion Hanger – Furnished with a 3/4" to 1/2" reducer for 1/2" stems				
	1/2	3/4 or 1/2	1.4 to 5.4 (3 to 12)	ALT50-12
	3/4	3/4 or 1/2		ALT7575-12
	1	3/4 or 1/2		ALT1075-12
	1/2	3/4 or 1/2	5.4 to 21.6 (12 to 48)	ALT50-48
	3/4	3/4 or 1/2		ALT7575-48
	1	3/4 or 1/2		ALT1075-48
	1/2	3/4 or 1/2	21.6 to 54 (48 to 120)	ALT50-120
	3/4	3/4 or 1/2		ALT7575-120
	1	3/4 or 1/2		ALT1075-120

POLES/HANGERS: NEC/CEC ORDINARY LOCATION FLEXIBLE FIXTURE HANGERS

