

AGUB and NGUB Instrument and Meter Enclosures

Explosionproof, Dust-Ignitionproof

Furnished with aluminum body and solid or window cover.

NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 4X, 7BCD, 9EFG

ENCLOSURES AND JUNCTION BOXES: NEC/CEC EXPLOSIONPROOF ENCLOSURES

Maximum Number of Drilled and Tapped Conduit Entries

Side	Trade Size of Conduit										Catalog Number
	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"	2-1/2"	3"	3-1/2"	4"	
Long	2	2	-	-	-	-	-	-	-	-	443A
Short	2	2	-	-	-	-	-	-	-	-	
Long	3	2	-	-	-	-	-	-	-	-	555A
Short	3	2	-	-	-	-	-	-	-	-	
Long	3	3	2	2	2	1	-	-	-	-	664A
Short	3	3	2	2	2	1	-	-	-	-	
Long	5	4	4	3	3	2	-	-	-	-	976A
Short	4	3	3	2	2	2	-	-	-	-	
Long	5	5	4	3	3	2	-	-	-	-	984A
Short	5	5	4	3	3	2	-	-	-	-	
Long	6	5	4	3	3	2	-	-	-	-	1093A
Short	5	4	4	3	3	2	-	-	-	-	
Long	6	5	5	4	3	3	2	2	-	-	10105A
Short	6	5	5	4	3	3	2	2	-	-	
Long	6	5	4	3	3	2	2	2	-	-	10106A
Short	6	5	4	3	3	2	2	2	-	-	
Long	6	5	4	3	3	2	2	2	1	1	10108A
Short	6	5	4	3	3	2	2	2	1	1	
Long	7	6	5	4	4	3	2	2	2	1	12128A
Short	7	6	5	4	4	3	2	2	2	1	
Long	7	6	5	4	4	3	2	2	2	1	121212A
Short	7	6	5	4	4	3	2	2	2	1	

Ordering Information for Drilled and Tapped Enclosures

For custom arrangement, see Modifications and Accessories and use the Custom Drill and Tap Schedule.

Grounding Kits

Catalog Number		Wire Capacity
Appleton	O-Z/Gedney	Al-Cu/Tinned Copper
AGK-04	NGK-04	#14-4 AWG
AGK-10	NGK-10	#8-1/0 AWG
AGK-25	NGK-25	#6 AWG-250MCM

Replacement Window Covers

Appleton		O-Z/Gedney	
Catalog Number	Use With Box Catalog Number	Catalog Number	Use With Box Catalog Number
ASW-443A	AGUBSW-443A	NSW-443A	NGUBSW-443A
ASW-555A	AGUBSW-555A	NSW-555A	NGUBSW-555A
ASW-664A	AGUBSW-664A	NSW-664A	NGUBSW-664A
ASW-976A	AGUBSW-976A	NSW-976A	NGUBSW-976A
ASW-984A	AGUBSW-984A	NSW-984A	NGUBSW-984A
ASW-1093A	AGUBSW-1093A	NSW-1093A	NGUBSW-1093A
ASW-10105A	AGUBSW-10105A	NSW-10105A	NGUBSW-10105A
ASW-10106A	AGUBSW-10106/8A	NSW-10106A	NGUBSW-10106/8A
ASW-12128	AGUBSW-12128/12A	NSW-12128	NGUBSW-12128/12A