

Code•Master™ 2 HID Factory Sealed Floodlights

Marine (Outside Type). Explosionproof

Integrally Ballasted. 150 W, 250 W, 400 W HPS; 150 W, 175 W, 250 W, 320 W, 350 W, 400 W PSMH; 175 W, 250 W, 400 W MH. Mogul Base.

NEC:
Class 1, Division 1 and 2, Groups C, D
Marine Type Electric Fixtures
Outside Type (Salt Water)

CEC:
Class I, Division 1 and 2, Groups B, C, D
Class II, Division 1, Groups E, F, G
Class II, Division 2, Groups F, G
Class III
CSA 4X

Applications

- UL Listed for Marine Type Electric Fixtures Outside Type (Salt Water).
- Ideal in Class I, Division 1 and 2 installations in refineries, in pipeline transportation facilities, at drilling rigs and in production facilities on land and marine platforms.
- Class I, Division 1 areas include:
 - (1) enclosed derricks, mud tanks, desander-desilter, gas-operated control devices, oil-gas separation vessels, shale shakers and flowing or beam wells
 - (2) flowing or beam wells in open areas with cellar or below grade sump
 - (3) on refinery docks where tankers are loaded with hoses or loading arms
 - (4) in compressor buildings (open or enclosed) where methane gas is present
- Virtually all enclosed areas at drilling operations or refineries where ventilation is inadequate, or where a cellar or below grade sump exists, are Class I, Division 1.

Features

- Choice of mountings: (1) crossarm with degree indicator; (2) junction box for horizontal or vertical mount; and (3) swivel for pole mount (screws onto standard 2" pipe threads).
- Fixtures operate safely in high ambient temperatures. For example, in Class I areas the 150 W HPS unit operateSee page 1290 for classified area suitability.
- Arrangement of heat-producing components results in more efficient heat dissipation for cooler fixture operation.
- All threaded joints are flame-tight.
- Five threads are always fully engaged in an explosionproof manner.
- Factory sealed. External seals not required.
- Strategic location of lamp socket, in combination with the interior prism design of the glass globe, provides optimum light distribution and control.
- Heat- and impact-resistant globes have smooth dust-resistant exterior.
- Superior corrosion resistance, with epoxy powder coat finish.
- Ballasts operate at low temperatures – PSMH: -29 °C (-20 °F); HPS: -40 °C (-40 °F).

Standard Materials

- Ballast housing, guard and junction box, and pole mounts: copperfree (4/10 of 1% max.) aluminum
- Crossarm mount: malleable iron
- Trunnion: steel.
- High bay reflector: aluminum
- Standard dome, deep dome and 30° angle reflectors: fiberglass reinforced polyester
- Socket: porcelain
- Screw shell: nickel-plated phosphor bronze

Standard Finishes

- Ballast housing, guard, trunnion and mounting accessories: epoxy-clad finish. Powder coat baked finish, electrostatically applied for complete, uniform corrosion protection



Shown with Optional High Bay Reflector

Effective Protected area: 1.8 Square Feet

Options

- Fuses for field installation are ordered by catalog number from the fuse kit table
- Quartz Auxiliary Emergency Lamp for PSMH and HPS fixtures. Relay switch installed fixture. Add suffix **-E** to fixture catalog number.
- Hot Restrike Option available for 150 W HPS. Add suffix **-R**.
- Smart Starter. Add suffix **-S**

NEC/CEC Certifications and Compliances

- UL Standard: UL 1598, UL 844
- UL Listed: E10794
- CSA Standard: C22.2 No. 250, C22.2 No. 137
- CSA Certified: 025428

Code•Master™ 2 HID Factory Sealed Floodlights

Marine (Outside Type). Explosionproof

Integrally Ballasted. 150 W, 250 W, 400 W HPS; 150 W, 175 W, 250 W, 320 W, 350 W, 400 W PSMH; 175 W, 250 W, 400 W MH. Mogul Base.

NEC:

Class 1, Division 1 and 2, Groups C, D
Marine Type Electric Fixtures
Outside Type (Salt Water)

CEC:

Class I, Division 1 and 2, Groups B, C, D
Class II, Division 1, Groups E, F, G
Class II, Division 2, Groups F, G
Class III
CSA 4X

Classified Area Suitability — Suitability includes use of reflector

Lamp Type	Lamp Watts	Supply Wire °C (°F)	Ambient Temp °C (°F)	Class I, Division 1 and 2 With Globe or with Globe and Reflector UL/NEC/CEC Temp. Ident. No.			Class II, Division 1 and 2 With Globe or with Globe and Reflector CEC Temp. Ident. No.	
				Nameplate Marking	NEC Groups	CEC Groups	Nameplate Marking	CEC Groups
High Pressure Sodium	150	50 (122)	40 (104)	T5	C,D	B, C, D	T3A	E,F
	150	75 (167)	55 (131)	—	C,D	B, C, D	T3	—
	250	75 (167)	40 (104)	T4	C,D	B, C, D	—	—
	250	75 (167)	55 (131)	—	C,D	B, C, D	—	—
	400	85 (185)	40 (104)	T3A	C,D	B, C, D	—	—
Pulse Start Metal Halide	175	75 (167)	40 (104)	T3B	C,D	B, C, D	T3C	E,F,G
	250	75 (167)	40 (104)	T3B	C,D	B, C, D	T3A	E,F
	320	75 (167)	40 (104)	T3	C,D	B, C, D	—	—
	350	75 (167)	40 (104)	T3	C,D	B, C, D	—	—
	400	75 (167)	40 (104)	T3	C,D	B, C, D	—	—
Metal Halide ①	175	75 (167)	40 (104)	T4	—	B, C, D	T3C	E, F, G
	250	75 (167)	40 (104)	T4	—	B, C, D	T3A	E, F
	400	75 (167)	40 (104)	T3C	—	B, C, D	—	—

① Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.

Code•Master™ 2 HID Factory Sealed Floodlights

Marine (Outside Type). Explosionproof

Integrally Ballasted. 150 W, 250 W, 400 W HPS; 150 W, 175 W, 250 W, 320 W, 350 W, 400 W PSMH. Mogul Base.

NEC:
Class 1, Division 1 and 2, Groups C, D
Marine Type Electric Fixtures
Outside Type (Salt Water)

Appleton

HID/FLOODLIGHT: NEC/CEC EXPLOSIONPROOF

	Lamp Watts	ANSI Lamp Type		Catalog Number ①③	
		HPS	PSMH	HPS	PSMH
Fixture Unit					
Furnished with Trunnion 3/4" hub. (3/4 – 14 NPT)					
	150	S55	M102	CFL150MT	CFP150MT
	175	—	M137/M152	—	CFP175MT
	250	S50	M138/M153	CFL250MT	CFP250MT
	320	—	M145	—	CFP320MT
	350	—	M131	—	CFP350MT
	400	S51	M135/M155	CFL400MT	CFP400MT
Fixture Unit with Junction Box for Horizontal or Vertical Mounting ②					
3/4" fixture hub and two conduit openings (3/4 – 14 NPT). 30" Flexible Coupling connects to 3/4" fixture hub and to 1/2" junction box opening. Furnished with one 3/4" Close-up Plug. Has Locking Screw for horizontal adjustment.					
	150	S55	M102	CFL150JBMT	CFP150JBMT
	175	—	M137/M152	—	CFP175JBMT
	250	S50	M138/M153	CFL250JBMT	CFP250JBMT
	320	—	M145	—	CFP320JBMT
	350	—	M131	—	CFP350JBMT
	400	S51	M135/M155	CFL400JBMT	CFP400JBMT
Fixture Unit with Pole-Top Mount (on 2" Threaded Pipe) ②					
2" tapered threads (2 – 11-1/2 NPT). Locking Screw for horizontal adjustment. 30" Flexible Coupling connects to 3/4" fixture hub (3/4 – 14 NPT) and to 1/2" pole-top opening (1/2-14 NPT).					
	150	S55	M102	CFL150SFMT	CFP150SFMT
	175	—	M137/M152	—	CFP175SFMT
	250	S50	M138/M153	CFL250SFMT	CFP250SFMT
	320	—	M145	—	CFP320SFMT
	350	—	M131	—	CFP350SFMT
	400	S51	M135/M155	CFL400SFMT	CFP400SFMT
Fixture Unit with Crossarm Mounting ②					
For mounting to flat surface. 180° horizontal adjustment with degree indicator. 30" Flexible Coupling connects to 3/4" fixture hub (3/4 – 14 NPT) and to any 1/2" opening (1/2 – 14 NPT).					
	150	S55	M102	CFL150CAMT	CFP150CAMT
	175	—	M137/M152	—	CFP175CAMT
	250	S50	M138/M153	CFL250CAMT	CFP250CAMT
	320	—	M145	—	CFP320CAMT
	350	—	M131	—	CFP350CAMT
	400	S51	M135/M155	CFL400CAMT	CFP400CAMT

① To order fixture with guard, add suffix **-G** before voltage suffix.

② Fixtures furnished with trunnion and bolts, flexible coupling and fittings, and mounting accessory. The trunnion provides vertical adjustment and the mounting accessory provides horizontal adjustment.

③ Change suffix **-MT** (120/208/240/277 V) to **-480** for 480 V.

Code•Master™ 2 HID Factory Sealed Floodlights




Marine (Outside Type). Explosionproof

Integrally Ballasted. 150 W, 250 W, 400 W HPS; 150 W, 175 W, 250 W, 320 W, 350 W, 400 W PSMH; 175 W, 250 W, 400 W MH. Mogul Base.

NEC:
Class 1, Division 1 and 2, Groups C, D
Marine Type Electric Fixtures
Outside Type (Salt Water)

CEC:
Class I, Division 1 and 2, Groups B, C, D
Class II, Division 1, Groups E, F, G
Class II, Division 2, Groups F, G
Class III
CSA 4X

Dimensions in Millimeters (Inches)



Weights kg (lb)

150 W	175 W	250 W	320 W	350 W	400 W
21 (46.30)	21 (46.30)	32 (70.55)	32 (70.55)	32 (70.55)	32 (70.55)

Code•Master™ 2 HID Factory Sealed Floodlights

Marine (Outside Type). Explosionproof

Typical Footcandle Values for Iso-Footcandle Curves. Data Based on 400 W HPS (50,000 Lumens) Clear Mogul Base Lamps.

NEC:


Class 1, Division 1 and 2, Groups C, D
 Marine Type Electric Fixtures
 Outside Type (Salt Water)

CEC:

Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1, Groups E, F, G
 Class II, Division 2, Groups F, G
 Class III
 CSA 4X


Photometric Data

400 W HPS Floodlight at 45° Angle with High Bay Reflector ①





Mounting Height (feet)	FOOTCANDLE VALUES FOR ISO-FOOTCANDLE CURVES								
	A	B	C	D	E	F	G	H	I
15	52.52	43.34	31.00	17.05	10.23	4.77	2.43	1.36	0.84
20	29.54	24.38	17.44	9.59	5.75	2.68	1.37	0.77	0.47
25	18.91	15.60	11.16	6.14	3.68	1.72	0.87	0.49	0.30
30	13.13	10.84	7.75	4.26	2.56	1.19	0.61	0.34	0.31
35	9.65	7.96	5.69	3.13	1.88	0.88	0.45	0.25	0.15
40	7.39	6.10	4.36	2.40	1.44	0.67	0.34	0.19	0.12

400W MH Floodlight at 45° Angle with High Bay Reflector



Mounting Height (feet)	FOOTCANDLE VALUES FOR ISO-FOOTCANDLE CURVES								
	A	B	C	D	E	F	G	H	I
15	33.97	22.10	16.12	9.69	6.40	4.12	2.13	1.13	.67
20	19.11	12.43	9.07	5.45	3.60	2.31	1.20	.64	.38
25	12.23	7.96	5.80	3.49	2.30	1.48	.77	.41	.24
30	8.49	5.52	4.03	2.42	1.60	1.03	.53	.28	.17
35	6.24	4.06	2.96	1.78	1.18	.76	.39	.21	.12
40	4.78	3.11	2.27	1.36	.90	.58	.30	.16	.10



① For 250 Watt HPS Clear, 30,000 Lumen lamp, multiply all FTC values by 0.60.