

# Code•Master™ Jr. HID Factory Sealed Luminaires

Explosionproof, Dust-Ignitionproof

Hazardous Locations. Medium Base. For use with threaded metal conduit.

Integrally Ballasted. 50 W, 70 W, 100 W, 150 W HPS; 175 W PSMH. 50 W, 70 W, 100 W, 150 W, 175 W MH ①


NEC: Class I, Division 1 and 2, Groups B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Marine type electric fixtures, outside type (salt water)  
CEC: Class I, Division 1 and 2, Groups B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Type 4X | Exd IIB + H<sub>2</sub>

## Applications

- For use in chemical and petrochemical plants, such as manufacturers of plastics, paints and thinners; in refineries; and in other areas where ignitable vapors, dust, moisture and corrosive elements may be present.
- Suitable for outdoor saltwater locations and for other wet locations.

## Features

- Fixtures operate safely in high ambient temperatures.
- Arrangement of heat-producing components results in efficient heat dissipation for cooler fixture operation.
- Patented “wireless” design. Threading of fixture unit onto mounting hood makes electrical connection. Only wiring required is attaching two wires to connection block in mounting hood.
- Connection block is easily wired: (a) loosen two screws, (b) make wire connections, and (c) re-position connection block.
- Safe, easy servicing without disconnecting any wiring. “Wireless” fixture unit threads off mounting hood for convenient servicing or for immediate replacement with a “stand-by” unit.
- Acme double-lead threads speed installation and fixture removal from mounting hood – only half as many turns are required as for single-lead threads. The threads do not stick or gall, eliminating problems often encountered with single-lead threads during fixture unit removal.
- All threaded joints are flame-tight.
- Integrally ballasted HID lighting fixtures; separate ballasts not required.
- Factory sealed. External seals not required for Groups C and D.
- Fixtures for use in NEC Group B locations furnished complete with UL required sealing fitting. Not required for CEC approval.
- Strategic location of lamp socket, in combination with interior prism design of the glass globe, provides optimum light distribution and control.
- Heat and impact-resistant globes have smooth dust-resistant exterior.
- Superior corrosion resistance, with epoxy powder coat finish.
- Shock-absorbing medium-base socket mounts prolong lamp life.
- Porcelain socket with nickel-plated phosphor bronze screw shell. Assures long trouble-free operation in high ambient areas.
- Choice of mountings: pendant, ceiling, bracket and stanchion.
- Fiberglass-reinforced polyester reflectors, in standard dome, or 30° angle styles, are ideal in installations where luminaire is subject to exceptionally severe corrosive atmospheres.
- Optional guards protect globes from damage. Secured to fixture with three stainless steel screws.
- Variety of light sources: high pressure sodium, pulse start metal halide and metal halide. HPS is excellent where long lamp life is required. HPS provides high lumens per watt and is less expensive to operate. PSMH and MH are desirable where colors in illuminated areas must be close to natural.
- A wide range of ballasts and voltages are available for both domestic and export applications.
- Ballasts operate at low temperatures – PSMH/MH: -29 °C (-20 °F); HPS: -40 °C (-40 °F).
- 50 W through 150 W high pressure sodium ballasts are high reactance, high power factor type.



## Standard Materials

- Ballast bodies and guards: copperfree (4/10 of 1% max.) aluminum
- Pendant mounting hoods: diecast copperfree (4/10 of 1% max.) aluminum
- Ceiling, bracket and stanchion mounting hoods: sand cast copperfree (4/10 of 1% max.) aluminum
- Reflectors: fiberglass reinforced polyester

## Standard Finishes

- Ballast bodies, guards and mounting hoods: epoxy powder coat finish, electrostatically applied for complete, uniform corrosion protection

## Options

- Fuses: order fuses for field installation by catalog number, see *Ballast and Fuse Kit Data*.
- Emergency Options available for 50 W through 150 W HPS only.
- For CEC Exd IIB + H<sub>2</sub> rating, add suffix **-Z**.
- For safety chain, add suffix **-SC**.

## NEC/CEC Certifications and Compliances

- UL Standard: UL 1598, UL 844
- UL Listed: E10444
- CSA Standard: C22.2 No. 250, C22. 2No. 137
- CSA Certified: 025428

① Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.

# Code•Master™ Jr. HID Factory Sealed Luminaires

Explosionproof, Dust-Ignitionproof

Hazardous Locations. Medium Base. For use with threaded metal conduit.

Integrally Ballasted. 50 W, 70 W, 100 W, 150 W HPS; 175 W PSMH. 50 W, 70 W, 100 W, 150 W, 175 W MH ①

NEC: Class I, Division 1 and 2, Groups B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Marine type electric fixtures, outside type (salt water)

CEC: Class I, Division 1 and 2, Groups B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Type 4X | Exd IIB + H<sub>2</sub>

HID Luminaires | Area / Task | Explosionproof, Hazardous Location | NEC / CEC

		Description	Catalog Number
<b>Polyester Reflectors</b>			
		Standard Dome 30° Angle	KR2-ST KR2-AN
Standard Dome	30° Angle		
<b>Prismatic Glass Globe and Ring Assembly — 50 W through 175 W</b>			
			CJGL-175
<b>Aluminum Guards — 50 W through 175 W</b>			
			CJGU-15
<b>Replacement Sockets — 50 W through 175 W</b>			
		Medium base sockets	CJMS-175
<b>Connection Block — 50 W through 175 W</b>			
		For all Code•Master fixtures	VPT-7

① Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.