

ALPF Factory Sealed Lighting – APPF Power Distribution Panelboards

Explosionproof, Dust-Ignitionproof, Watertight

NEC:

Class I, Division 1 and 2, Groups B♦, C♦, D

Class II, Division 1 and 2, Groups E, F, G

Class III

Class I, Zone 1, Group IIB +H₂

NEMA 4, 4X, 7BCD, 9EFG

Applications

- Distribution panelboards are used to furnish protection and control of electrical equipment in hazardous locations. These compact units provide a centrally controlled switching system for large quantities of branch circuits for:
 - Lighting
 - Heating
 - Small motors
 - Similar electrical equipment

Features

- Breaker operators included as standard.
- O-ring gasket insures watertight integrity.
- Factory sealed, no external seals are required for most branch circuits. All conduits must be sealed adjacent to enclosure for Class I, Division 1, Groups B and C.
- Breakers are housed in the panel section and prewired to maximum circuit capacity, then wired to numbered terminals in the wiring compartment.
- Terminal compartment is interconnected to panel section with sealing hubs, unions and poured with sealing compound.
- Permits selection of 1-, 2- or 3-pole breakers.
- Precision machined flame path between body and cover.
- Bolt on stainless steel slotted mounting feet.
- Breaker operators can be padlocked in the ON or OFF position.
- All panelboards are supplied with Cutler-Hammer [†] interiors.
- Chassis assemblies with mains at top (bottom optional).
- Provisions for 12, 18, 24, 30, 36 and 42 circuit 1-pole chassis.
- 100 Amp or 225 Amp main lug.
- Up to 100 Amp backfed main breaker available with main lug chassis.
- Up to 225 Amp main breaker available with main breaker chassis.
- Factory installed ground and neutral bar as standard.

Standard Materials

- Bodies and covers: copperfree (4/10 of 1% max.) aluminum
- Cover bolts: Quad-Lead®, captive, stainless steel
- Breaker operators: copperfree (4/10 of 1% max.) aluminum
- Hinges: stainless steel
- Bus bars: copper
- O-ring: neoprene

Standard Finish

- Corrosion resistant gray epoxy powder coat to provide NEMA 4X rating

Options


Must be listed in alphanumeric sequence at the end of the catalog number.

- Panel Options
 - Breather, NEMA 4X add suffix —**BR**.
 - Drain, NEMA 4X add suffix —**DN**.
 - External ground stud add suffix —**EGS**.
 - Grounding neutral lug add suffix —**GNL**.
 - Terminal breaker located at bottom, add suffix —**INV**.
 - Main breaker located at bottom, add suffix —**LB**.
 - Phenolic nameplate (specify legend) add suffix —**NP**.
 - For 50 °C (122 °F) breaker rating, add suffix —**V**.
 - For stainless steel terminal enclosure for Division 2 applications only, contact your local sales representative.

♦ For Class I, Division 1, Groups B and C, all conduits must be sealed within 50.8 mm (2") of enclosure.

[†] Cutler-Hammer is a trademark of the Eaton Corporation.

① GFI Push-to-Test Buttons are standard with GFI or EPD options.



- Main Breaker Options
 - Auxiliary switch (1A or 1B) add suffix —**AS1**.
 - Auxiliary switch (2A or 2B) add suffix —**AS2**.
 - Shunt trip (specify voltage) add suffix —**ST**.
 - Under voltage release (specify voltage) add suffix —**UV**.
- Branch Breaker Option ALPF Only
 - Equipment Protection Devices (1- or 2-Pole -30 mA sensitivity) ① add suffix —**EPD**.
 - Ground Fault Interrupter (1- or 2-Pole -5 mA sensitivity) ① add suffix —**GFI**.
 - GFI Indicating Light add suffix —**L5**.
- Branch Breaker Options APPF GHB Only
 - Equipment Protection Devices (1- or 2-Pole -30 mA sensitivity) ① add suffix —**EPD**.
- Branch Breaker Options APPF F-Frame Only
 - Auxiliary switch (1A or 1B) add suffix —**AS1**.
 - Auxiliary switch (2A or 2B) add suffix —**AS2**.
 - Shunt trip (specify voltage) add suffix —**ST**.
 - Under voltage release (specify voltage) add suffix —**UV**.
- 400 Amp panel available, contact your local sales representative.

NEC Certifications and Compliances

- UL Standard: UL 1203
- UL Classified: E84577

APPF Series Power Distribution Panelboards

Explosionproof, Dust-Ignitionproof, Watertight

GHB Cutler-Hammer + Circuit Breakers

NEC:

Class I, Division 1 and 2, Groups B♦, C♦, D

Class II, Division 1 and 2, Groups E, F, G

Class III

Class I, Zone 1, Group IIB +H₂

NEMA 4, 4X, 7BCD, 9EFG

Select GHB + branch breakers as desired in panel. First and second digits are the quantity of breakers, third and fourth digits are ampere rating, the fifth digit is number of poles. Example: An 18-circuit 277/480 V 3-phase 4-wire 100 A MLO panel with 12 1-pole 20 Amp and 3 2-pole 30 Amp branch breakers should read APPFK14C18ML100-12201EPD-03302.

Catalog Numbering Guide

APPF	K	1	4	C	18	ML	100	12	20	1	EPD		▲
Duty: Appleton Factory Sealed Power Panel			Voltage: 4 - 277/480 (3P 4W Only) 7 - 24 Vdc 8 - 125/250 Vdc			Main Type: MB - Main Breaker ML - Main Lug Only			Ampere Rating ①: 15 - 15AT 20 - 20AT 25 - 25AT 30 - 30AT 35 - 35AT 40 - 40AT 45 - 45AT 50 - 50AT 55 - 55AT 60 - 60AT 70 - 70AT 80 - 80AT 90 - 90AT 100 - 100AT			Additional Branch Breakers: Repeat Step ①	
Panel Size: J - 12 Circuit, 100 Amp Main Lug Only K - 18 Circuit, 100 Amp Main Lug Only M - 30 Circuit, 100 or 225 Amp Main Lug Only or 18 Circuit with Main Breaker N - 42 Circuit, 225 Amp Main Lug Only or 36 Circuit with Main Breaker Q - 42 Circuit with Main Breaker			Wire System: C - 3P, 4W D - 2P, 2W for 24 Vdc			Ampere Rating: 020 - 20AT 025 - 25AT 030 - 30AT 040 - 40AT 050 - 50AT 060 - 60AT 070 - 70AT 080 - 80AT 090 - 90AT 100 - 100AT 110 - 110AT 125 - 125AT 150 - 150AT 175 - 175AT 200 - 200AT 225 - 225AT			No. of Poles ①: <i>(include only if different from wiring system)</i>			Suffix for Other Options/ Features: Must be listed in alphanumeric sequence <i>(See Options)</i>	
		Current Rating: 1 - 100 Amp 2 - 225 Amp			Number of Circuits: 12 18 24 30 36 42			Quantity of Branch Breakers ①: 1 thru 42			Breaker Type ①: Normal Duty (Leave Blank) EPD ①		

① EPD Single Phase (requires 2-Poles) 277 Vac, 30 mA.

♦ For Class I, Division 1, Groups B and C, all conduits must be sealed within 50.8 mm (2") of enclosure.

▲ Suffix for Other Options/Features: Must be listed in alphanumeric sequence. See Options.

+ GHB and Cutler-Hammer are trademarks of the Eaton Corporation.

ALPF Factory Sealed Lighting – APPF Power Distribution Panelboards

Explosionproof, Dust-Ignitionproof, Watertight

F-Frame Cutler Hammer + Circuit Breakers

NEC:

Class I, Division 1 and 2, Groups B ♦, C ♦, D

Class II, Division 1 and 2, Groups E, F, G

Class III

Class I, Zone 1, Group IIB +H₂

NEMA 4, 4X, 7BCD, 9EFG


DISTRIBUTION EQUIPMENT: NEC/CEC HAZARDOUS LOCATION PANELBOARDS

APPLETON™

ALPF and APPF (GHB Type) Factory Sealed Distribution Panelboard

Panel Size	Sealed Together		Top Outlets	Side Outlets	Mounting Hdw. Set
N	153707	161606/08	(1) 3" and (8) 1" NPT	(4) 1" NPT	AMH8
Q	184207	181806/08	(1) 3" and (8) 1" NPT	(4) 1" NPT	AMH8

Dimensions in Millimeters (Inches)



Panel Size	A1	A2	B1	B2	C1	C2	D1	D2	E	F1	F2	G	H	K	M
N	501.7 (19.75)	498.6 (19.63)	279.4 (11.00)	812.8 (32.00)	539.8 (21.25)	533.4 (21.00)	539.8 (21.25)	1090.7 (42.94)	1705.1 (67.13)	69.9 (2.75)	130.3 (5.13)	101.6 (4.00)	66.8 (2.63)	100.1 (3.94)	330.2 (13.00)
Q	552.5 (21.75)	584.2 (23.00)	330.2 (13.00)	974.9 (38.38)	593.9 (23.38)	603.3 (23.75)	593.9 (23.38)	1212.9 (47.75)	1882.9 (74.13)	96.8 (3.81)	157.2 (6.19)	101.6 (4.00)	88.9 (3.50)	127.0 (5.00)	325.4 (12.81)

♦ For Class I, Division 1, Groups B and C, all conduits must be sealed within 50.8 mm (2") of enclosure.