

# Code•Master™ Factory Sealed Strobe Luminaires

## Explosionproof, Dust-Ignitionproof


**NEC:**  
 Class I, Division 1 and 2, Groups C, D  
 Class I, Division 2, Groups A, B  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 NEMA 3R, 4X

**NEC:**  
 Suitable for Wet Locations  
 Marine Outside Type (Saltwater)

### Ordering Information

Order using catalog numbering guide below or select catalog number from tables on following pages.

### Catalog Numbering Guide



### Thermal Suitability of Code-Master Strobe Fixture

Ambient Temp. °C (°F)	Class I, Division 1 and 2 Groups C and D	Class I, Division 2 Groups A and B	Class II, Division 1 and 2 Class III
40 (104)	T6	T2B	T4A
55 (131)	T6	T2B	T4A
65 (149)	T6	T2A	T4

### Operating Temperatures

"T" Numbers Represent the Maximum Internal Temperature for Class I, Division 2 Locations; Maximum Surface Temperature for Class I, Division 1 Locations; and Maximum Surface Temperature Under Dust Blanket for Class II, Division 1 Locations.

"T" Number	T1	350	325	T2	T2A	T2B	T2C	T2D	T3	T3A	T3B	T3C	T4	T4A	T5	T6
Temp. Range (°C)	351-450	326-350	301-325	281-300	261-280	231-260	216-230	201-215	181-200	166-180	161-165	136-160	121-135	101-120	86-100	85
Temp. Range (°F)	664-842	619-662	574-617	538-572	502-536	448-500	421-446	394-419	358-392	331-356	322-329	277-320	250-275	214-248	187-212	185

NOTE: The maximum operating temperature of the fixture must not exceed the ignition temperature of the gas, vapor or dust to be encountered per the National Electrical Code.

① UL1971: Hearing-Impaired Strobe Only  
 ② Not for use with UL1971 Strobe  
 ③ Diode Polarized (Current limiter supplied as standard).

# Code•Master™ Factory Sealed Strobe Luminaires

Explosionproof, Dust-Ignitionproof

**NEC:**  
 Class I, Division 1 and 2, Groups C, D  
 Class I, Division 2, Groups A, B  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 NEMA 3R, 4X

**NEC:**  
 Suitable for Wet Locations  
 Marine Outside Type (Saltwater)

## Strobes for the Hearing Impaired

	Type Mounting	Volts	Catalog Number — UL1971: Hearing-Impaired ①
<b>Pendant — One Hub 3/4" NPT, Rigid Conduit</b>			
		20-30 Vdc	CSSP752030DCCLP
<b>Ceiling — Four Hubs 3/4" NPT, Three Close-Up Plugs, Rigid Conduit</b>			
		20-30 Vdc	CSSC752030DCCLP
<b>Fixture Unit Only — Less Mounting Hood</b>			
		20-30 Vdc	CSSB752030DCCLP
<b>Fixture Unit Only — Less Mounting Hood</b>			
	4.7 kg (10.36 lb)	20-30 Vdc	CSST2030PDCCL
	Weight kg (lb)	Hub Size (Inches)	Catalog Number — UL1971: Hearing-Impaired
<b>Pendant Mounting Hood — One Hub 3/4" NPT, Rigid Conduit</b>			
	9.0 (19.84)	3/4	CAP-751971
<b>Ceiling Mounting Hood — Four Hubs 3/4" NPT, Three Close-Up Plugs, Rigid Conduit</b>			
	1.8 (3.97)	3/4	CAC-751971
<b>Bracket Mounting Hood — Four Hubs 3/4" NPT, Three Close-Up Plugs, Rigid Conduit</b>			
	2.7 (5.95)	3/4	CALB-751971

① Only clear globes are available for UL1971 applications.