

ATX™ D Series Aluminum Control Stations

Flameproof

ATEX:
 Zone 1 and 2 – 21 and 22
 Ⓢ II 2 GD
 IP66 – IK10

Applications

- Local control stations for use in hazardous areas.
- Control of electrical equipment at power plants, chemical and petrochemical plants, petroleum refineries, pulp and paper processing plants and various industrial applications.

Features

- 1 and 2 Function Ex d IIC:
 - Supplied with actuators, contact blocks and pilot lights.
 - TS35 rail mounted contact blocks.
 - Threaded flameproof joint.
 - Connection: 2 x 2.5 mm² (0.004 in²) maximum.
 - Internal earth: 2 x 4 mm² (0.006 in²).
 - External ground: M5
 - 1 x M20 or M25 threaded entry at bottom.
 - Cable glands and plugs to be ordered separately.
- 2 and 3 Function Exd IIB:
 - Supplied with actuators and rail mounting pilot lights and contact blocks.
 - Flanged flameproof joint.
 - Yellow laminated plastic legend plate with black lettering.
 - Connection : 2 x 2.5 mm² (0.004 in²) maximum.
 - Internal earth: 2 x 4 mm² (0.006 in²).
 - External earth: M6 screw.
 - 2 x M20 threaded entries at the bottom.
 - Cable glands and plugs to be ordered separately.

Standard Materials

- Box: gray painted marine grade aluminum alloy

Options

- For other configurations, see pre-drilled control stations or consult factory.

ATEX Certifications and Compliances

- Certification Type BR1d
 - Gas, Zones 1 and 2
 - Conforming to ATEX 94/9/CE: Ⓢ II 2 G
 - Type of Protection: Ex d IIC
 - Temperature Class: T6 for Ta = +40 °C (+104 °F), T5 for Ta = +55 °C (+131 °F)
 - Dust, Zones 21 and 22
 - Conforming to ATEX 94/9/CE: Ⓢ II 2 D
 - Type of Protection: Ex tD A21
 - Surface Temperature: T95 °C (T203 °F)
 - Ambient Temperature: -40 °C to +55 °C (-40 °F to +131 °F)
 - CE Declaration of Conformity: 20530
 - ATEX Certificate: LCIE 02 ATEX 6056
- Certification Type CF2D
 - Gas, Zones 1 and 2
 - Conforming to ATEX 94/9/CE: Ⓢ II 2 G
 - Type of Protection: Ex d IIB
 - Temperature Class: T6 for Ta ≤ +40 °C (+104 °F), T5 for +40 °C (+104 °F) < Ta ≤ +55 °C (+131 °F)
 - Dust, Zones 21 and 22
 - Conforming to ATEX 94/9/CE: Ⓢ II 2 D
 - Type of Protection: Ex tD A21
 - Surface Temperature: T95 °C (T203 °F)
 - Ambient Temperature: -40 °C to +55 °C (-40 °F to +131 °F)
 - CE Declaration of Conformity: 50254
 - ATEX Certificate: LCIE 03 ATEX 6061X

- Index of Protection according EN/IEC 60529: IP66
- Impact Resistance (shock): IK10
- Internal Volume: ≤ 2 dm³ (122 in³) - 2 liters

EURASEC Certification

- EURASEC RU C-FR. Г505.В.00911

Other Certification ①

- INMETRO Certificate: BVC 11.0482

1 Function



2 Function



2 Function



3 Function



① INMETRO certification available on special request only. Contact your local sales representative for more information.

ATX™ D Series Aluminum Control Stations

Flameproof

ATEX:
Zone 1 and 2 – 21 and 22
II 2 GD
IP66 – IK10

Appleton

CONTROLS: ATEX/IECEx FLAMEPROOF CONTROL STATIONS AND RELAYS

Type	Description/Function	Bottom Entries	Weight kg (lb)	Volume dm ³ (in ³)	Catalog Number
1 Function Ex d IIC Control Stations					
Spring Return Push Button					
	BR1d 1x black spring return push button with 1NO + 1NC momentary contacts	1 x M20	1.0 (2.20)	3.75 (24.41)	DA1W1T101
	BR1d 1x black spring return push button with 1NO + 1NC momentary contacts	1 x M25	1.0 (2.20)	3.75 (24.41)	DA1W3T101
Mushroom Head Push Button					
	BR1d 1x red mushroom head push-pull with 1NO + 1NC maintained contacts Padlockable in both positions	1 x M20	1.2 (2.65)	3.75 (24.41)	DA1W1T102
	BR1d 1x red mushroom head push-pull with 1NO + 1NC maintained contacts Padlockable in both positions	1 x M25	1.2 (2.65)	3.75 (24.41)	DA1W3T102
	BR1d Red mushroom head key release with 1NO + 1NC maintained contact Unlocked with key (MS1)	1 x M20	1.2 (2.65)	3.75 (24.41)	DA1W1T104
	BR1d Red mushroom head key release with 1NO + 1NC maintained contact Unlocked with key (MS1)	1 x M25	1.2 (2.65)	3.75 (24.41)	DA1W3T104
Time Delayed Push Button 230 V 50/60 Hz					
	BR1d 1x time delayed black impulse push button adjustable from 25s to 15mn For 1000 W incandescent or 400 W fluorescent max.	1 x M20	1.2 (2.65)	3.75 (24.41)	DA1W1T103
	BR1d 1x time delayed black impulse push button adjustable from 25 s to 15 mn For 1000 W incandescent or 400 W fluorescent max.	1 x M25	1.2 (2.65)	3.75 (24.41)	DA1W3T103
Twin Push Buttons					
	BR1d 1x green spring return 'I' push button with 1NO momentary contact 1x red spring return 'O' push button with 1NC momentary contact	1 x M20	1.2 (2.65)	3.75 (24.41)	DA1W1T201
	BR1d 1x green spring return 'I' push button with 1NO momentary contact 1x red spring return 'O' push button with 1NC momentary contact	1 x M25	1.2 (2.65)	3.75 (24.41)	DA1W3T201
2 Function Ex d IIB Control Stations					
Twin Push Buttons					
	CF2D 1x green spring return 'I' push button with 1NO momentary contact 1x red spring return 'O' push button with 1NC momentary contact	2 x M20	2.5 (5.51)	7.00 (427.17)	DA2W2T201
	CF2D 1x green spring return 'I' push button with 1NO momentary contact 1x red mushroom head push-pull with 1NO+1NC maintained contacts	2 x M20	2.5 (5.51)	7.00 (427.17)	DA2W2T202