

EF and FHS Series Flexible Fixture Hangers

Hook and Loop

UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.

CEC: Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of lighting fixtures.

Features

- Protect fixture against wind and vibration damage.
- EF hook and loop hangers
 - Malleable iron for strength and safety.
 - Hook and loop combination permits quick disconnect and removal of fixture for maintenance.
 - Offer inexpensive means of pendant flexible suspension of lighting fixtures.
 - Permit free swing in any direction.
 - EF jaw openings can be completely closed for added safety.
- FHS support hangers
 - Provide up to 75.3 kg (166 lbs) support for fixtures on the non-electrical side of mounting.
 - Straddle a maximum of 1-1/4" conduit and accepts 1/2" or 3/4" fixture hook or conduit.

Standard Materials

- Malleable iron



EFHM



EFHF



FHS

Standard Finishes

- Zinc electroplate and clear chromate

CEC Certifications and Compliances

- CSA Certified: 065180

	Support Weight in kg (lbs)	Size (Inches)	Length A mm (in)	Weight in kg (lbs)	Catalog Number
EF — Safety Support Hooks — With 3/8" jaw opening					
	EFHM—Male				
	40.9 (90)	1/2	66.8 (2.63)	0.08 (0.19)	EFHM-50
		3/4	74.7 (2.94)	0.07 (0.32)	EFHM-75
	EFHF—Female				
40.9 (90)	1/2	50.8 (2.00)	0.07 (0.16)	EFHF-50	
	3/4	52.1 (2.05)	0.08 (0.19)	EFHF-75	
FHS — Support for Fixtures, Dummy Side — Straddles up to 1-1/4 trade size conduit — 11/32" diameter mounting holes, spaced 3-1/4" apart					
	75.3 (166)	1/2 or 3/4	87.1 (3.31)	0.39 (0.85)	FHS5075

Dimensions in Millimeters (Inches)

	Catalog Number	A	B	C
	EFHM-50	1/2-14 NPT	50.8 (2.00)	66.8 (2.63)
	EFHM-75	3/4-14 NPT	54.1 (2.13)	73.2 (2.88)
	EFHF-50	1/2-14 NPT	50.8 (2.00)	—
	EFHF-75	3/4-14 NPT	54.1 (2.13)	—