

EDS Series Factory Sealed Manual Motor Starters and Contactors

Explosionproof, Dust-Ignitionproof

NEC/CEC:

Class I, Division 1 and 2, Groups C, D
Class II, Division 1 and 2, Groups E, F, G
Class III
NEMA 3, 3R, 7CD, 9EFG

Applications

- Manual motor starters are available to meet any plant installation requirement.
- They may be used to install a variety of electrical wiring devices and comes complete with covers and dead-end or feed-thru hub arrangements. Available with or without heater.
- Complete units are ideal for manual starting of small Vac or Vdc motors in locations made hazardous by the presence of flammable vapors, gases or combustible dust.

Features

- Easily readable operator handle with provisions for padlocking in the ON or OFF position.
- Cast in hubs.
- Interchangeable heater units.

Standard Materials

- Body and cover: malleable iron
- Sealing chamber: copperfree (4/10 of 1% max.) aluminum
- Operating handle: nylon

Standard Finishes

- Body and cover: gray epoxy powder coat

Options

- For Aluminum Backbox and Cover add suffix **-A**.
- Starters are furnished with one interchangeable heater. Select heater number from heater selection table and add appropriate suffix to catalog number. For example, a complete catalog number with Allen-Bradley ◀ motor starter and Allen-Bradley ◀ 0-17 amp heater: EDS150-1MSAB-AB1.

NEC/CEC Certifications and Compliances

- UL Standards: UL 508, UL 698, UL 1203
- CSA Standards: C22.2 No 14-M, C22.2 No. 25, C22.2 No. 30
- cULus Listed: E76550, E81751



1-Gang
Dead-End



2-Gang
Feed-Thru

CONTROLS: NEC/CEC EXPLOSIONPROOF MOTOR STARTERS

Appleton

◀ Allen-Bradley is a registered trademark of Rockwell Automation.

Visit our website at www.emerson.com or contact us at (800) 621-1506.
© November 2016

EDS Series Factory Sealed Manual Motor Starters and Contactors

Explosionproof, Dust-Ignitionproof

NEC/CEC:
 Class I, Division 1 and 2, Groups C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 3, 3R, 7CD, 9EFG



Factory Sealed Manual Motor Starters

Poles	Hub Size (Inches)	Catalog Number Cover/Chamber/Device		1-Gang Catalog Number ②		2-Gang Catalog Number ②	
		Allen Bradley ◀ ①	Cutler-Hammer + ①	Dead-End	Feed-Thru	Dead-End	Feed-Thru
1	1/2			EDS150-1MS	EDSC150-1MS	EDS250-1MS	EDSC250-1MS
	3/4	EDK1MSAB	EDK1MSW	EDS175-1MS	EDSC175-1MS	EDS275-1MS	EDSC275-1MS
	1			EDS110-1MS	EDSC110-1MS	EDS210-1MS	EDSC210-1MS
2	1/2			EDS150-2MS	EDSC150-2MS	EDS250-2MS	EDSC250-2MS
	3/4	EDK2MSAB	EDK2MSW	EDS175-2MS	EDSC175-2MS	EDS275-2MS	EDSC275-2MS
	1			EDS110-2MS	EDSC110-2MS	EDS210-2MS	EDSC210-2MS

Manual Motor Starter Horsepower Ratings

Poles	120-240 Vac	32 Vdc	120 Vdc	240 Vdc	Allen-Bradley ◀ Catalog Number	Cutler-Hammer + Catalog Number
1	1 HP	—	—	—	Bulletin 600	—
2	1 HP	—	3/4 HP	3/4 HP	Bulletin 600	—
1	1 HP	1/4 HP	—	1/4 HP	—	MST01
2	1 HP	1/4 HP	1 HP	1 HP	—	MST02

EFD Non-Factory Sealed Manual Contactors — No Heater Options

Poles	Hub Size (Inches)	Catalog Numbers		Description	Switch Ratings
		Dead-End	Feed-Thru		
2	1/2	EFD150-2MS	EFDC150-2MS	SQUARE D Class 2510, Type KO-1	30 Amp, 250 Vac/Vdc; 20 Amp, 600 Vac; 1 HP, 115 Vac; 2 HP, 230 Vac; 3 HP, 460-575 Vac
	3/4	EFD175-2MS	EFDC175-2MS		
	1	EFD110-2MS	EFDC110-2MS		
3	1/2	EFD150-3MS	EFDC150-3MS	ARROW-HART AH7810-UD	30 Amp, 600 Vac; 3 HP, 120 Vac; 7-1/2 HP, 240 Vac; 15 HP, 480 Vac; 15 HP 600 Vac
	3/4	EFD175-3MS	EFDC175-3MS		
	1	EFD110-3MS	EFDC110-3MS		

Non-Factory Sealed Components

Poles	Description	Catalog Number
—	Cover only	EFKMSQ
2	Device only	EFS2MSQ
3	Device only	EFS3MSQ

+ Cutler-Hammer is a registered trademark of Eaton Corporation.

◀ Allen-Bradley is a registered trademark of Rockwell Automation.

① For heaters, see following page.

② **Ordering Instructions:** Add suffix **-AB** to catalog number for Allen-Bradley motor starter; add suffix **-W** for Cutler-Hammer motor starter. Starters are furnished with one interchangeable heater. Select heater number from heater selection table and add appropriate suffix to catalog number. For example, a complete catalog number with Allen-Bradley motor starter and Allen-Bradley heater: **EDS150-1MSAB-AB1**. For Aluminum Backbox and Cover add suffix **-A**.

EDS Series Factory Sealed Manual Motor Starter and Contactor Heaters

Allen-Bradley and Cutler-Hammer heaters and starters are not interchangeable with each other.

NEC/CEC:

Class I, Division 1, Groups C, D
 Class I, Division 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 3, 3R, 7CD, 9EFG

The "Full Load Motor Current" listed in the tables below are ratings which determine the proper heat element that should be used with the EDS Series starters. Refer to motor nameplate for its full load motor current. It is our recommendation that for normal conditions the heater element selected should have a capacity of 20 to 25% greater than the full load current of the motor. This applies to standard +40 °C (+104 °F) temperature rise motors. For +50 °C (+122 °F) rise motors, a heater not greater than 115% full load current should be selected.

However, due to the difference between full load motor currents of various motor manufacturers of the same size motors, the above information is approximate.

If selection of heater element is uncertain as might be in the case of a motor subject to frequent starting and intermittent load, it is advisable to contact the starter manufacturer or his local representative giving full particulars, such as motor horsepower, voltage, phase cycles, name or manufacturer or pertinent data that may aid in the selection of the proper heater element.

Allen-Bradley ◀

Full Load Motor Current (Amp)	Add Suffix EDS
0.17	-AB1
0.21	-AB2
0.25	-AB3
0.32	-AB4
0.39	-AB5
0.46	-AB6
0.57	-AB7
0.71	-AB8
0.79	-AB9
0.87	-AB10
0.98	-AB11
1.08	-AB12
1.19	-AB13
1.30	-AB14
1.43	-AB15
1.58	-AB16
1.75	-AB17
1.88	-AB18
2.13	-AB19
2.40	-AB20
2.58	-AB21
2.92	-AB22
3.09	-AB23
3.32	-AB24
3.77	-AB25
4.16	-AB26
4.51	-AB27
4.93	-AB28
5.43	-AB29
6.03	-AB30
6.83	-AB31
7.72	-AB32
8.24	-AB33
8.90	-AB34
9.60	-AB35
10.80	-AB36
12.00	-AB37
13.50	-AB38
15.20	-AB39

Cutler-Hammer †

Full Load Motor Current (Amp)	Heater Rating (Amp)	Add Suffix EDS
0.40-0.43	0.50	-WH1
0.44-0.48	0.55	-WH2
0.49-0.53	0.61	-WH3
0.54-0.58	0.67	-WH4
0.59-0.64	0.74	-WH5
0.65-0.71	0.81	-WH6
0.72-0.78	0.89	-WH7
0.79-0.87	0.98	-WH8
0.88-0.95	1.10	-WH9
0.96-1.03	1.20	-WH10
1.04-1.15	1.30	-WH11
1.16-1.27	1.45	-WH12
1.28-1.35	1.60	-WH13
1.36-1.51	1.70	-WH14
1.52-1.67	1.90	-WH15
1.68-1.83	2.10	-WH16
1.84-1.99	2.30	-WH17
2.00-2.23	2.50	-WH18
2.24-2.47	2.80	-WH19
2.48-2.71	3.10	-WH20
2.72-2.95	3.40	-WH21
2.96-3.27	3.70	-WH22
3.28-3.59	4.10	-WH23
3.60-3.99	4.50	-WH24
4.00-4.39	5.00	-WH25
4.40-4.79	5.50	-WH26
4.80-5.26	6.00	-WH27
5.27-5.83	6.60	-WH28
5.84-6.39	7.30	-WH29
6.40-7.03	8.00	-WH30
7.07-7.74	8.80	-WH31
7.75-8.46	9.70	-WH32
8.47-9.35	10.60	-WH33
9.36-10.30	11.70	-WH34
10.31-11.35	12.90	-WH35
11.36-12.47	14.20	-WH36
12.48-13.67	15.60	-WH37
13.68-15.12	17.10	-WH38
15.13-16.00	18.60	-WH39

† Cutler-Hammer is a registered trademark of Eaton Corporation.

◀ Allen-Bradley is a registered trademark of Rockwell Automation.

CONTROLS: NEC/CEC EXPLOSIONPROOF MOTOR STARTERS

Appleton®