


ATX™ FD Series Cylindrical Fluorescent Luminaires

Standard and Emergency Battery Back-Up. Flameproof

ATEX/IECEX:
 Zone 1 and 2 - 21 and 22
 II 2 GD
 IP66/68

FLUORESCENT/AREA: ATEX/IECEX STANDARD AND EMERGENCY BACK-UP

Accessories and Replacement Parts

	Description	Catalog Number
External Reflector – White Painted Galvanized Steel		
	Model 0.3	FDER1G
	Model 0.6	FDER2G
	Model 1.2	FDER3G
	Model 1.5	FDER4G
Protective Guard – Zinc Plated Steel		
	Model 0.3	FDPG1Z
	Model 0.6	FDPG2Z
	Model 1.2	FDPG3Z
	Model 1.5	FDPG4Z
Fixing Brackets for Ease of Surface Installation – Set of Two		
	Zinc plated steel	FDFBZ
	316 stainless steel	FDFBS
Surface Mounting Brackets – Set of Two		
	Zinc plated steel	FDSBZ
	316 stainless steel	FDSBS
Half Clamp Brackets for Pole Mounting – Set of Two		
	Pole diameter 42 to 49 mm (1.65 to 1.93 in) Tube diameter 31.8 to 38.1 mm (1.25 to 1.5 in)	
	Zinc plated steel	FDHC49Z
	316 stainless steel	FDHC49S
	Pole diameter 60 mm (2.36 in) Tube diameter 50.8 mm (2 in)	
	Zinc plated steel	FDHC60Z
	316 stainless steel	FDHC60S
Fall Prevention Kit		
	1.20 meter (3.94 foot) stainless steel chain	FDSCS