

Fixture Hanger Bracket and Accessories

UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.

NEC/CEC: Rated for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of lighting fixtures.

Features

- Fixture hanger brackets are suitable for use with fixtures with 3/4-14 NPT conduit openings or hubs. Mounts directly to ceiling or wall separately from conduit system. Catalog number includes two brackets and two hexhead bolts.
- Safety support hooks and rigid support for dummy side of lighting fixtures comes as a complete assembly; includes two hooks and one rigid support. Each hook is supplied with a screw for closing 3/8" jaw opening. Rigid support straddles maximum 1-1/4" conduit. (Chain shown in installation view not furnished.)
- SLC steel locking couplings are designed for use on 3/4" fixture stems. They feature a setscrew with an Allen head that fastens on the outside of the hub and fixture stem. It is used to prevent a fixture stem from turning in a hub that is not normally supplied with setscrews. For use in Class I, Division 1 installations when combined with conduit bodies (without set screws in hubs) to meet requirements of NEC Article 501.130(A)(3).

Standard Materials and Finishes

- Fixture hanger brackets iron with gray epoxy finish
- Safety support hook/rigid support: zinc electroplated malleable iron
- SLC steel locking couplings: steel with natural finish



FHS1




AC-KT




SLC75

Illustrated Features



Ceiling mounted FHS1 fixture hanger bracket projects light downward (90°). Shown mounted to Appleton AH260-118 explosionproof fluorescent lighting fixture.



Wall mounted FHS1 fixture hanger bracket projects light at 45° angle. Shown mounted to Appleton AH260-118 explosionproof fluorescent lighting fixture.



AC-KT hook and rigid support Installation View
(Chain shown in installation view not furnished)



SLC locking coupling installation view.

Fixture Hanger Bracket and Accessories

UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.

NEC/CEC: Rated for Ordinary (Unclassified) Locations

LED Luminaires | Mounting Hangers | Hazardous Location | NEC/CEC

Fixture Hanger Accessories

Description	Support Weight in kg (lbs)	NPT Size (Inches)	Weight in kg (lbs)	Catalog Number
Fixture Hanger Brackets				
 <p>Includes two brackets and two hexhead bolts</p>	90.0 (200)	3/4	2.93 (6.45)	FHS1
Safety Support Hooks and Rigid Support for Dummy Side of Lighting Fixtures				
 <p>Includes two hooks and one rigid support.</p>	40.0 (90.0)	3/4	0.68 (1.50)	AC-KT
SLC Steel Locking Couplings				
 <p>Includes two locking setscrews with Allen heads</p>	—	3/4	0.14 (0.30)	SLC75
	—	1	0.07 (0.16)	SLC1075

Dimensions in Millimeters (Inches) — FHS1 Fixture Hanger Bracket

