

# GRUE Universal Conduit Outlet Boxes

## Explosionproof, Dust-Ignitionproof

UNILETS™ for use with Threaded Metal Conduit. Furnished with Internal Ground Screw.

### NEC/CEC:

Class I, Division 1 and 2, Groups C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III

### Applications

- Complies with a wide range of classified area requirements.
- Corrosion-resistant: ideal indoors or out.
- For pulling of wires.
- Connect conduit lengths and change direction of conduit runs.
- Provide access for maintenance.

### Features

- Accurately tapped, tapered hub threads for tight, rigid joints and ground continuity.
- Furnished with covers.
- General purpose wiring.
- Universal design with five threaded universal hubs and three close-up plugs.
- Copperfree aluminum body and cover provide resistance to corrosive atmospheres.
- Covers have pry notches for bar or wrench.
- Smooth, rounded integral bushing in each hub type box protects conductor insulation.

### Standard Materials

- Bodies and covers: copperfree (4/10 of 1% max.) aluminum

### Standard Finishes

- Bodies and covers: epoxy powder coat


### NEC Certifications and Compliances

- UL Standard: UL 886 (UL 1203)
- UL Listed: E85310
- CSA Standard: C22.2 No. 25, C22.2 No. 30
- CSA Certified: 025875

Furnished with internally threaded aluminum surface cover, five threaded hubs, and three close-up plugs.  
For Form numbers designate body and matching cover sizes.

	Conduit Size (Inches)	Cover Body Opening mm (in)	Capacity dm <sup>3</sup> (in <sup>3</sup> )	Catalog Number
	1/2	85.9 (3.38)	0.22 (13.5)	GRUE50-A
	3/4	85.9 (3.38)	0.22 (13.5)	GRUE75-A
	1	85.9 (3.38)	0.29 (17.5)	GRUE100-A ①

### Dimensions in Millimeters (Inches)



Hub Size Inches	Dimensions in Millimeters (Inches)						
	A	B	C	D	E	F	G
1/2	108.0 (4.25)	57.2 (2.25)	69.9 (2.75)	17.5 (0.69)	36.6 (1.44)	103.1 (4.06)	52.3 (2.06)
3/4	108.0 (4.25)	57.2 (2.25)	69.9 (2.75)	17.5 (0.69)	36.6 (1.44)	103.1 (4.06)	52.3 (2.06)
1	108.0 (4.25)	62.0 (2.44)	76.2 (3.00)	23.9 (0.94)	38.1 (1.50)	138.2 (5.44)	57.2 (2.25)

① Not UL or CSA certified.